


MM	IN
1.52	.010
2.79	.106
3.14	.110
3.39	.130
3.74	.137
4.48	.170
5.49	.215
6.17	.240

TSE 1034

356-5307



RATINGS AT 12V DC	
IGN CIRCUIT	10 AMPS
START	5

METRIC

- NOTE
1. SHAFT O-RING SEALED TO CASE
 2. TERM INSUL GASKET SEALED
 3. ALL STEEL PARTS PLATED 11T W/DIC-50M, PL DIP OR CAL 17
 4. APPLICABLE SAE STANDARD OR RECOMMENDED PRACTICE SAE J259

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPRV D	SCALE	DATE DRAWN
									CF	11-20-78		1:1	1-10-66
				G	LEN # 60139	3/1/00	KF	FINISH					DATE BLUEPRINT
				F	CADU Y 125239	12/18/92	14						
				E	HOUSING	8-17-82	13	TOLERANCES					
				D	REDRAWN	11-8-78	R	FRACTIONAL ±					
								DECIMAL ± .25					
3 POS IGNITION & START SW													956-5307

CH-188 (4-78)