





MM.	IN.
0.25	.010
3.17	.125
6.35	.250
12.7	.500
19.05	.750
25.4	1.000
31.75	1.250
38.1	1.500
44.45	1.750
50.8	2.000
57.15	2.250

COLE-HERSEE CO.

NPM 4-7-65 EX 13918

APPLICABLE SAE STANDARD OR RECOMMENDED
PRACTICE SAE J259

95037



NOTES:

1. Ⓢ DENOTES SILVER LAM. RIVET
2. MELAMINE LINER
3. ALL SHOULDER RIVETS
4. ALL TERMINALS BRASS
5. FOR TO RMP 12 VOLT LOAD FROM 'B' TO 'S'
6. "O" RING SEALED AT MTG BUSHING
7. ALL STEEL PARTS PLATED

METRIC

LEGEND	
I	IGNITION (FULL VOLTAGE)
L	LIGHT SWITCH
B	BATTERY
S	START
F	FUEL & IGN. (THRU EXTERNAL RESISTANCE)

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRWN	CHECKED	APPR'D.	SCALE	DO NOT SCALE	
									MF	FA-17		FULL	DATE DRAWN	3-23-65
													DATE BLUEPRINT	
													COLE-HERSEE COMPANY	
													JSTON, MASS. 02127, U.S.A.	
													IGNITION & START SW.	
													95037	