


MM	IN
11.43	450
22.42	883
41.70	1641
75.00	2,950
0.8mm ²	18GA
3.86	152
4.01	158
6.37	251
6.43	253
8.50	335
8.63	340


74600-02



NEGATIVE GROUND
ONLY

METRIC

BLACK	GROUND
WHITE	LOAD
RED	BATTERY
WIRE COLOR	CIRCUIT



FRONT VIEW (B)
OF KNOB

- NOTES:
1. 12 VOLTS D.C. (14.7 VOLTS MAX)
4 AMPS MAX (UNIT NOT LOAD SENSITIVE)
LAMP OR RESISTIVE LOAD NEGATIVE GROUND ONLY
(GROUND WIRE (BLACK) MUST BE GROUNDING)
 2. PROTECTED FOR REVERSE POLARITY
(30 V D.C.)
 3. WEATHERPROOF SEALED
 4. ALL STEEL PARTS PLATED (A)

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPROVED	SCALE	DATE DRAWN	
									VAK			11	10-3-84	
				C	ECN 24372	6/1/84	BL	FINISH	 Cole Hersee Co. 36 OLD COLON VENUE BOU BOB OIL MA S.A. 02 1					DATE BLUEPRINT
				B	ECN 23482	4 8 87	1/2							
				A	23272	10-21-86	AF	TOLERANCES	SWITCH, DIMMER, 4 AMP					74600-02
				1	ISSUED	1 31 86	CS	DECIMAL ± METRIC ±						

CH-100(4-78)

Confidential Property of Cole Hersee