

MM	IN.
125	.010
3.17	.125
6.35	.250
22.09	.870
47.24	1.860
36.57	1.440
67.31	2.650

"OFF"

40°

"ON"IGN.

2 KEYS, RINGED, BRASS

FACE NUT, BRASS, CHROME PLT.

BUSHING, 13/16-24UNS-2A, BRASS

LOCKWASHER, INT. TOOTH, STEEL

HEX NUT, (M)

CASE, STEEL

TERM. INSULATOR, BAKELITE

TERMINAL, STEEL

SCREW, 8-32UNC-2A X 6.35 LG. & LOCKWASHER, STEEL (2 REQ'D)

CH 502

COLE-HERSEE BOSTON

22.09

3.17 DIA. HOLE

47.24 REF.

67.31 REF.

BAT

SIGN

ST

36.57 REF.

NOTE:
① ALL STEEL PARTS PLATED

METRIC

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPR'D.	SCALE	DATE DRAWN
				M	ECN 06023	2/2/66	SG	—//—	PH	TY 5-6-77		1:1	12-11-61
				L	CAD OR ZINC 125234	11/1/92	JH	FINISH —//—	COLE-HERSEE COMPANY BOSTON, MASS. 02127, U.S.A.				DATE BLUEPRINT
				K	ECN 23394	2-2-87	LJ						
				J	REV 1/9872	3-8-77	SG	TOLERANCES FRACTIONAL ±	2 POSITION IGNITION SW.				95532
				H	REV 2/9872	5-6-77	SG	DECIMAL ±					