


PART No.	WIRE GA. / COLOR	"A" (REF)	"B"	"C"
OFNY0002ZXJ	# 12 ORANGE	266.7 (10.5)	9.65±2 (.38)	9.65±2 (.38)



- NOTES:
- 1. DIMENSION "A" MEASURED WITH FUSE INSTALLED.
 - 2. MAX RATING: 30A, 32VDC.
 - 3. MAX. TEMPERATURE: 80°C.
 - 4. WIRE: COPPER STRANDED, GXL.
 - 5. CONTACTS: C1100 ALLOY.
 - 6. CRIMP: MUST MEET USCAR 21 STANDARD.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

CPK DENOTES CPK DIMENSIONS.-MINIMUM CPK VALUE

CPK DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. (PROCEDURE FOR MEASUREMENT OF CPK IS LOCATED IN THE FUSE INSPECTION INSTRUCTIONS.

CPK DENOTES CP DIMENSIONS.-MINIMUM CP VALUE

CPK DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. (PROCEDURE FOR MEASUREMENT OF CPK IS LOCATED IN THE FUSE INSPECTION INSTRUCTIONS.

CPK DENOTES CP DIMENSIONS.-MINIMUM CP VALUE

CPK DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. (PROCEDURE FOR MEASUREMENT OF CPK IS LOCATED IN THE FUSE INSPECTION INSTRUCTIONS.

COPIES TO		MATERIAL SPEC		FINISH		SCALE		DATE		SUPER DRW		RAW STK WT		LBS/M		TOLERANCE UNLESS OTHERWISE SPECIFIED		FRACTION ±		ANGULAR ±1°		TITLE		FUSEHOLDER, INLINE (WITH FUSE)		REVISION		DRAWING NO.		OUTLINE							
1	9	18	DRW	DHM	DATE	09/05/08	1=1	2	10	19	CHK	DATE	3	12	20	APD	DATE	4	13	21	5	14	23	6	15	33	7	16	43	8	17	53	000490ER-RELEASED 9/05/08	DHM	A	OFNY0002ZXJ	OFNY0002ZXJ

UNCONTROLLED DOCUMENT