





LED PILOT LIGHTS



LEGEND PLATE




PUSH BUTTON



MOUNTING DETAIL

NOTES:

1. DIMENSIONS IN MILLIMETRES (INCHES).
2. ----- INDICATES CLEARANCE REQUIRED.
3. PANEL THICKNESS 1.0 TO 6.0 (0.04 TO 0.24).
4. NEMA 4X.



CONNECTION DIAGRAM

NOTES:

1. RK-332 COMPONENTS ARE NOT POLARITY SENSITIVE.
2. SEE SE-330 MANUAL FOR MORE INFORMATION.
3. MANUALS ARE AVAILABLE AT www.startco.ca

RK-332

REMOTE INDICATION AND RESET FOR SE-330

- 2 - LED PILOT LIGHTS, RED: 24-120 Vac/ dc
 1 - PUSH BUTTON ASSEMBLY, YELLOW: 3 A @ 240 Vac - A600
 0.5A @ 125 Vdc - Q600

- 1 - "RESET" LEGEND PLATE
 1 - "RESISTOR FAULT" LEGEND PLATE
 1 - "GROUND FAULT" LEGEND PLATE



Copyright © 2011
 Printed in Canada
 181011