



MM IN

0.25	.010
0.96	.038
1.52	.060
1.82	.072
6.35	.250
7.92	.312
12.70	.500
11.93	.470
13.71	.540
14.98	.590
15.06	.593
15.87	.625
28.57	1.125

RATING:

10 AMPS @ 250 V. A. C.
 15 AMPS @ 125 V. A. C.
 25 AMPS @ 12 V. D. C.

55015



NOTE

1. ALL STEEL PARTS EITHER ZINC PLATE WITH DICHROMATE DIP OR CADMIUM PLATE
 2. SILVER CONTACT SURFACES

METRIC

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPR'D	SCALE	DATE DRAWN
								#	PLB	5-3-79		1:1	9 - 6 - 56
								FINISH					DATE BLUEPRINT
				L	ADD NOTE / 25432	7/15/93	JH	#					
				K	.531/21279	1-21-81	JB	TOLERANCES					
				J	REDRAWN	5-2-79	JV	DECIMAL ±					
								METRIC ± 0.25					
SP-DT TOGGLE SWITCH													55015

CH-188(4-78)