





- NOTES:
 1. MATERIAL: SILICON RUBBER
 2. GRAY COLOR
 3. 30 DURE HARD ◎

METRIC
COMPONENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
◎	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
COPIES TO		MATL SPEC SEE NOTES		
1 9 18		FINISH N/A		
2 10 19		DRW E JIN		
3 12 20		DATE 03/29/12		
4 13 21		SCALE 1:1		
5 14 23		CHK		
6 15 33		DATE		
7 16 43		SUPER DR		
8 17 53		APPD		
		DATE		
		FINSH GOOD WT		
		GRAMS/PIECE		
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)				
DIMENSION		0.5 - 3		
		UP TO 3 - 6		
		UP TO 6 - 30		
		UP TO 30 - 120		
		UP TO 120 - 400		
TOLERANCE				
3RD ANGLE PROJECTION		TITLE		
		BLANK_2 CABLE SEAL		
		REVISION		
DES PLAINES, ILLINOIS 60016		DRWG. NO.		
		A		
		OL - 868 - 954		

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED