


COLE-HERSEE CO.


| MM    | IN    |
|-------|-------|
| 0.25  | .010  |
| 2.28  | .090  |
| 7.87  | .310  |
| 9.65  | .380  |
| 10.28 | .405  |
| 10.41 | .410  |
| 15.87 | .625  |
| 20.82 | .820  |
| 26.67 | 1.050 |
| 32.51 | 1.280 |
| 60.70 | 2.390 |
| 14.22 | .560  |

APPLICABLE SAE STANDARD OR  
RECOMMENDED PRACTICE SAE J 253

| LEGEND |            |
|--------|------------|
| B      | BATTERY    |
| T      | TAIL LITES |
| H      | HEAD LITES |
| P      | PARK LITES |



DETAIL OF "O" RING SEAL  
OF MNTG. STEM., 2X SCALE




B, T & H

B, T & P

"METRIC"

"OFF"



KNOB, BLACK PLASTIC  
IMPRINTED "LIGHTS"

14.22 DIA

NOTES:

1. ALL STEEL PARTS PLATED
2. "O" RING SEALED AT BUSHING.
3. GASKET SEALED AT TERM. INSULATOR.
4. SILVERED CONTACT SURFACES. DO NOT SCALE

| LET | WAS | DATE | BY | LET | WAS               | DATE     | BY  | MATERIAL      | DRAWN | CHECKED | APPR V D | SCALE | DATE DRAWN     |
|-----|-----|------|----|-----|-------------------|----------|-----|---------------|-------|---------|----------|-------|----------------|
|     |     |      |    | J   | ECN 25312         | 6/8/94   | J E | — # —         | MF    | ✓       |          | 1:1   | 3-25-65        |
|     |     |      |    | H   | 2 IN. 125234      | 11/7/76  | H H | FINISH        |       |         |          |       | DATE BLUEPRINT |
|     |     |      |    | G   | REV 120475        | 12/16/80 | G   | — # —         |       |         |          |       |                |
|     |     |      |    | F   | ADDED 20543       | 4-5-79   | JAV | TOLERANCES    |       |         |          |       |                |
|     |     |      |    | E   | NO DRAWING CHANGE | -17-18   | JAV | FRACTIONAL ±  |       |         |          |       |                |
|     |     |      |    |     |                   |          |     | DECIMAL ±0.25 |       |         |          |       |                |

COLE-HERSEE COMPANY  
BOSTON, MASS 02127, U.S.A.

LIGHTING SWITCH 72100