




THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.



REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PCO #5300103. INITIAL RELEASE. DSILVA	10/4/2022	L.ARGIL



- NOTES:
1. MATERIAL: COPPER, TIN PLATED.

NO.	COMPONENT NO.	COMPONENT NAME	QTY	U						
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)										
.5 to 3	>3 to 6	>6 to 30	>30 to 120	>120 to 400						ANGLE
±0.05	±0.05	±0.10	±0.15	±0.20						NONE

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.		
PER CHI-NPDP20-0008 PROCEDURE		FIT/ FUNCTION CRITICAL CHARACTERISTICS
		SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL
	CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE
		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
	CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

NAME		DATE	<div>Littelfuse</div> <div>Expertise Applied Answers Delivered</div> <div>TITLE</div> <div>STEPPED BUS BAR - FLEC TO FLEXMEGA</div>					
DRAWN	DSILVA	7/27/2022						
CHECKED	-	-						
	-	-						
FORM NO: CVP-PE40-0003 REV B								
THIRD ANGLE PROJECTION								
			SIZE B		DWG. NO. OUTLINE		REV. A	
DO NOT SCALE DRAWING			SCALE 2:1				SHEET 1 OF 1	