

USP3021 Thermistor Probe




Description

Littelfuse offers Stainless probe housings suitable for a wide range of temperature sensing applications. If the dimensions on this product won't work for your requirements, please contact us for further assistance.

Features

- Temperature Standard
- Supplied with NIST Traceable Calibration Cert
- 105°C Max Operating Temperature


Dimensions



Dimensions in inches.

A	B	C	D
15.5" ± 1.0"	9.50" ± 0.500"	0.250" ± 0.005"	Strip: 0.250" ± 0.070"

Part Numbering System



Note: Not all combinations of Part Number codes are available. Contact Littelfuse for details.

Specifications

Part Number	Resistance Ohms @ 25°C	Resistance Tol. ± % @ 25°C	R-T Curve	Temperature Coefficient (% / °C) @ 25°C	Beta (K) 0-50°C	Temperature Rating (°C)
USP3021	10000	2	J	-4.4	3892	-55 to +105

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: www.littelfuse.com/disclaimer-electronics