


| PART NUMBER | PACKAGING   |
|-------------|-------------|
| KR272G0J-1  | BULK        |
| KR272G0J-2  | TAPE & REEL |

RESISTANCE @ +25°C = 2,700  $\Omega$   $\pm$  5%  
 RESISTANCE/TEMPERATURE CURVE = SEE KR272G0J R-T TABLE  
 BETA " $\beta$ " (+25 TO +85°C) = 3,750°K NOMINAL  
 POWER RATING = 240 mW  
 TEMPERATURE RATING = -40 TO +125°C

PACKAGING: SEE TABLE

ROHS COMPLIANT

SEE MANUFACTURING SPECIFICATION (LAYER 1)



|      |                       |          |     |
|------|-----------------------|----------|-----|
| NONE | RELEASE TO PRODUCTION | 04/27/17 | DD  |
| REV  | REVISION RECORD       | DATE     | APP |

|          |             |                                                                                                           |
|----------|-------------|-----------------------------------------------------------------------------------------------------------|
| SCALE    | NONE        | U.S. SENSOR corp.<br>© COPYRIGHT<br>714-639-1000 www.ussensor.com<br>NTC CHIP THERMISTOR<br>P/N KR272G0J- |
| DRAWN BY | DAN DANKERT |                                                                                                           |
| DATE     | 04/27/17    |                                                                                                           |
| REV.     | NONE        |                                                                                                           |
| LAYER    | 0 OF 2      |                                                                                                           |