

FUSE SELECTION CHART

FUSE TYPE	MICRO2	ATO®	MINI®	MCASE®	JCASE®	MAXI	MIDI	MEGA®	PAL Series 0	PAL Series 1	PAL Series 2	PAL Series 5	ZCASE
Black		1A					175A			80A	80A		40A
Gray		2A	2A	15A			150A			120A	120A		60A
Violet		3A	3A 3A			100A	200A				140A <small>PAL SERIES 2 ONLY</small>		80A
Pink		4A	4A	30A	30A		125A	250A	30A	30A	30A		100A
Tan	5A	5A	5A 5A			70A	70A	225A					125A
Brown	75A	75A	75A 75A								70A <small>PAL SERIES 2 ONLY</small>	25A	150A
Red	10A	10A	10A 10A	50A	50A	50A	50A	80A	50A <small>PAL SERIES 0 ONLY</small>		50A <small>PAL SERIES 2 ONLY</small>		175A
Blue	15A	15A	15A 15A	20A	20A	60A	100A	200A	20A <small>PAL SERIES 0 ONLY</small>	100A	100A		200A
Yellow	20A	20A	20A 20A	60A	60A	20A	60A	100A	60A <small>PAL SERIES 0 ONLY</small>	60A	60A		225A
Clear	<small>MICRO 2 ONLY</small> 25A	25A	25A 25A	25A		80A	80A	80A			60A <small>PAL SERIES 2 ONLY</small>		250A
Green	<small>MICRO 2 ONLY</small> 30A	30A	30A 30A	40A	40A	30A	40A	125A	40A		40A	30A	300A
Orange		40A				40A	40A	150A					400A
White					25A		23A	175A			120A <small>PAL SERIES 4 ONLY</small>		500A
													600A

GLASS

AGU	AGC, SFE20, UK	AGX	SFE6
AGY, SFE30	SFE14	AGW, SFE7.5, SFE9	AGA, SFE4

AGA 1A, 1.5A, 2A, 2.5A, 3A, 5A, 6A, 7.5A, 10A, 15A, 20A, 25A, 30A	AGC .5A, 1A, 1.5A, 2A, 2.5A, 3A, 4A, 5A, 6A, 7.5A, 8A, 10A, 15A, 20A, 25A, 30A, 35A	AGU 1A, 2A, 3A, 4A, 5A, 10A, 15A, 20A, 25A, 30A, 35A, 40A, 50A, 60A	AGW 1A, 1.5A, 2.5A, 3A, 4A, 5A, 6A, 15A, 20A, 30A	AGX 2A, 3A, 20A, 25A, 30A	AGY 50A	SFE 4A, 6A, 7.5A, 9A, 14A, 20A, 30A	UK 35A, 50A
---	---	---	---	-------------------------------------	-------------------	---	-----------------------

FUSE HOLDER SELECTION CHART

FUSE TYPE	ATO®							MINI®			MAXI	GLASS	
ACTUAL FUSE SIZE													
PHOTO													
Series Name	FHAC1	FHAC2	FHA1	FHA2	FHA-GLO	AFH1	AFH1	FHM1	FHM2	FHM-GLO	MAH1	FNY1	FNY2
Holder Type	In-Line		In-Line		In-Line	In-Line Panel Mount		In-Line		In-Line	In-Line	In-Line	In-Line
Max Amperage	20A	30A	20A	30A	30A	20A	30A	20A	30A	30A	60A	20A	30A
Wire Color	Black	Orange	Black	Orange	Red	Black	Red	Black	Orange	Red	Black or Red	Black	Orange
Weatherproof	•	•			•			•	•	•	•	•	•
Notes	Standard	Heavy Duty	Standard	Heavy Duty	Smart-Glow	Standard	Heavy Duty	Standard	Heavy Duty	Smart-Glow	Standard	Standard	Heavy Duty
FUSE TYPE	JCASE® and Low Profile JCASE®				MIDI®			MEGA					
ACTUAL FUSE SIZE													
PHOTO													
Series Name	FHJC1	FHJC2	FHJ1	FHJ2	498	Compact-498	FLEX-MIDI	298	SN	FLEX-MEGA			
Holder Type	In-Line		In-Line		In-Line	In-Line	Bolt-Down	Bolt-Down	Bolt-Down	Bolt-Down			
Max Amperage	40A	60A	40A	60A	200A	200A	200A	500A	500A	500A			
Wire Color	Red	Red	Red	Red	-	-	-	-	-	-			
Weatherproof	•	•				with heat shrink			•				
Notes	Standard	Heavy Duty	Standard	Heavy Duty	Standard	Compact	Busbars Available	Standard	AssureLatch & IP69K	Busbars Available			