


- NOTES:
1. MAX. RATING 30A, 32 VOLTS AT A MAXIMUM OPERATING TEMPERATURE OF 82° C.
  2. BODY MATERIAL: ALCRYN, BLACK  
COVER MATERIAL: ALCRYN, BLACK
  3. WIRE: 12 GA, COLOR: ORANGE

CUSTOMER: FORD  
CUSTOMER P/N: YW1T-14517-AA

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
<b>BILL OF MATERIAL</b>				
COPIES TO		MATL SPEC	FINISH	
1	9	DRW	BJJ	SCALE 1:1
2	10	19	CHK	DATE 5/26/99
3	12	20	CHK	DATE SUPER DRW
4	13	21	APPD	DATE RAW STK WT
5	14	23		LBS/M
6	15	33		TOLERANCE UNLESS OTHERWISE SPECIFIED
7	16	43		TWO PLACE DEC ±.01 FRACTION ±
8	17	53		THREE PLACE DEC ±.005 ANGULAR ±1°
<b>TITLE</b>				
MINIFUSE HOLDER, IN LINE				
LTR		REVISION		CHK APD
A	07944	RELEASED		
	5/26/99	BJJ		
B	39954B	MODIFY DIMS., ADD CUSTOMER INFO		
	06/22/99	PJM		

  
 DES PLAINES, ILLINOIS 60016  
 DRAWING NO. 01530023Z  
 OUTLINE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

DENOTES CRITICAL CHARACTERISTICS.

DENOTES CPK DIMENSIONS--MINIMUM CPK VALUE ----

DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. THE PROCEDURE FOR MEASUREMENT OF THIS CHARACTERISTIC IS LOCATED IN THE INSTRUCTIONS.

DENOTES CP DIMENSIONS--MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS AND TOLERANCES SPECIFIED IN THE INSTRUCTIONS LOCATED TO THE DRAWING FOR MAXIMUM TOOL LIFE.

CONTROLLED DOCUMENT