



- NOTES:
1. MAX. RATING, 20 AMPS, 32 VOLTS AT A MAXIMUM OPERATING TEMPERATURE OF 82° C.
 2. BODY MATERIAL: ALCRYN, BLACK
COVER MATERIAL: ALCRYN, BLACK
 3. COVER TETHER IS SLID ON EITHER WIRE LEAD AND SEATED IN BODY GROOVE.
 4. FUSEHOLDER IS SHIPPED WITH COVER ATTACHED BUT NOT SNAPPED ON THE BODY.

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
MATL SPEC		FINISH		
COPIES TO	DRW	PJM	DATE	SCALE
1	9		10/15/01	1:1
2	10			
3	12			
4	13			
5	14			
6	15			
7	16			
8	17			
TOLERANCE UNLESS OTHERWISE SPECIFIED		LBS/M		
TWO PLACE DEC ±.01		SUPER DRW		
THREE PLACE DEC ±.005		RAW STK WT		
TITLE		MINIFUSE HOLDER, IN LINE		
LTR		REVISION		CHK
A	60683	RELEASE	10/15/01	PJM

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

CPK DENOTES CRITICAL CHARACTERISTICS.

CPK DENOTES CPK DIMENSIONS.-MINIMUM CPK VALUE

CPK DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. REFERENCE PROCEDURE FOR MEASUREMENT OF CPK IN THE INSTRUCTION MANUAL.

CPK DENOTES CP DIMENSIONS.-MINIMUM CP VALUE

CPK DENOTES DIMENSIONS WITHIN THE DIMENSIONAL LIMITATIONS AND TOLERANCES SPECIFIED IN THE DIMENSIONALLY LOCATED TO THE DRAWING FOR MAXIMUM TOOL LIFE.

CONTROLLED DOCUMENT

DES PLAINES, ILLINOIS 60016
 DRAWING NO. SERIES OUTLINE
 A 01530029Z