



NOTE:

ALL DIMENSIONS ARE IN MILLIMETERS,
ENGLISH DIMENSIONS ARE IN [].

CERTIFICATION OF
COUNTRY OF ORIGIN
REQUIRED

COPIES TO		MAT'L. SPEC.		FINISH		SCALE		SUPER. DR.		RAW STK. WT.		LBS./M	
1	2	3	4	5	6	7	8	9	10	11	12	13	14
18	19	20	21	23	33	43	53	TOLERANCE UNLESS OTHERWISE SPECIFIED					
9	10	12	13	14	15	16	17	TWO PLACE DEC. ± 0.50mm [0.020]					FRACTION ±
1	2	3	4	5	6	7	8	THREE PLACE DEC. ± 0.25mm [0.010]					ANGULAR ±
TITLE 4 POSITION MAXI FUSE MODULE													
Littelfuse® 800 E. NORTHWEST HIGHWAY DES PLAINES, ILLINOIS 60016													
DRWG. NO. E-03540505Z													
LTR		REVISION								CHK.		APPD.	
A		06534 - RELEASED October 10, 94 Ges.								Ges.		APP	
B		36644D - CHG - 2 PLACE TOLERANCE .010 TO .020 CHG 2 PLACE TOLERANCE .020 TO .010 2-10-95								Ges.		Ges.	
C		36988 L - ADD METRIC DIM'S 7-19-95 RFR								Ges.		Ges.	
D		37055D - CHG TITLE 8-19-95 JCU								TJR		Ges.	
E		000807E - 10-9-09 REINSTATE JCU											