


## Holder / No. 268

### PC Mount, 5x20mm Fuses leadfree

### Specifications



3mm Cap depth

#### Mounting

For direct soldering to PC Boards.  
Leads should not be twisted or bent closer than 3mm from the cap.  
Sharp bending of the leads can cause mechanical weakness followed by breaking of the leads.

#### Materials

Holder: Brass, nickel-plated  
Axial Leads: Copper, tin-plated for soldering

#### Electrical Data (23°C)

Rated Voltage: 250V  
Maximum Current: 8A

#### Minimum Cross Section

Conducting path - 0.2mm<sup>2</sup>

#### Unit Weight

0.3g

#### Packaging

Bulk (5000 pcs.)

#### Order Number

Holder

No. 268 0000 100


#### Order Information

Qty.	Order-Number	Series	Packaging
		268	0000 100

## Holder / No. 266

### PC Mount, 6.3x32mm Fuses leadfree

### Specifications



#### Mounting

For direct soldering to PC Boards.  
Leads should not be twisted or bent closer than 3mm from the cap.  
Sharp bending of the leads can cause mechanical weakness followed by breaking of the leads.

#### Materials

Holder: Brass, silver-plated  
Axial Leads: Copper, tin-plated for soldering

#### Electrical Data (23°C)

Rated Voltage: 250V  
Maximum Current: 8A

#### Minimum Cross Section

Conducting path - 0.2mm<sup>2</sup>

#### Unit Weight

0.4g

#### Packaging

Bulk (2000 pcs.)

#### Order Number

Holder

No. 266 0000 100

#### Order Information

Qty.	Order-Number	Series	Packaging
		266	0000 100

Note: 1.00 means the number one with two decimal places. 1,000 means the number one thousand.

Specifications are subject to change without notice.