


30155

MM	IN
13.46	.53
35.30	1.39
40.38	1.59
304.80	12.00
336.55	13.25
1mm <sup>2</sup>	16Ga




NOTE :  
I. REF. DIMENSIONS ONLY.

METRIC

DO NOT SCALE

BRUNING 40-21 63765

LET.	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPRV'D.	SCALE	DATE DRAWN
								$\#$	ZU	AF		1:1	8-14-87
								FINISH					DATE BLUEPRINT
								$\#$	 <small>20 OLD COLONY AVENUE, SOUTH BOSTON, MA, U.S.A. 02127</small>				
				A	ECN 24592	10/22/80	AF	TOLERANCES	DIMMER SWITCH SOCKET				30155
					ISSUED	8/31/87	AF	DECIMAL $\pm$ METRIC $\pm$					

CH-188(4-78)