


MM. IN
 15.87 .625
 43.18 1.700
 55.88 2.200
 322.50 12.700
 601.98 23.700
 906.78 35.700
 952.375

48000



EX19992

LABEL

- NOTES**
1. TRAILER GROUND NOT PROVIDED
 2. CONNECTORS SHIPPED LOOSE
 3. ALL WIRE LEADS 18 GA. GPT
 4. WIRE LEADS SHIPPED TIED (A)(B)
 5. ELECTRONICS ENCASED IN HENCOL #30

METRIC

DO NOT SCALE

LET.	WAS	DATE	BY	LET.	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPR'D	SCALE	DATE DRAWN
									DFG	RFB		1:1	2-8-83
								FINISH	 39 OLD COLONY AVENUE SOUTH BOSTON MA, U.S.A. 02137				DATE BLUEPRINT
				B	ECN 49559	12/11/79	JF						
				A	BANDED/22627	12-12-81	AK	TOLERANCES	TRAILER TAILLITE CONVERTER				48000
					ISSUED	5/23/82	RFB	DECIMAL ± .1					
								METRIC ± .25					

CH-188(4-78)