

Military Midget 10x38 mm Fuses

594 Series

Commercial Equivalent = [BLN Series](#)



Description

With a vast network of manufacturing and engineering facilities and a global system of distribution channels, Littelfuse offers a variety of switchgear fuses to meet your specific needs, including military high-reliability fuses.

Features & Benefits

FEATURES	BENEFITS
10x38 mm size	Common dimensions used in a variety of control circuit applications
Fast-acting	Provides fast short-circuit response within the interrupting rating
Fiber body	Cost effective materials provide a lower cost alternative for supplemental circuit protection
POWR-GARD® technology	Ensures reliable overcurrent protection

Applications

- Control circuits
- Military (MIL Grade) applications

Approved to MIL-PRF-15160

MIL TYPE DESIGNATION	NICKEL-PLATED CAPS	MIL TYPE DESIGNATION	NICKEL-PLATED CAPS
F09A 250V 1A	594 001	F09A 250V 15A	594 015
F09A 250V 2A	594 002	F09A 250V 20A	594 020
F09A 250V 3A	594 003	F09A 250V 25A	594 025
F09A 250V 4A	594 004	F09A 250V 30A	594 030
F09A 250V 5A	594 005		
F09A 250V 6A	594 006		
F09A 250V 7A	594 007		
F09A 250V 8A	594 008		
F09A 250V 10A	594 010		
F09A 250V 12A	594 012		

Note: Boldface numbers indicate series; light type numbers indicate amperage value.

Disclaimer Notice – Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/product-disclaimer.