


74600-02


MM	IN
11.43	.450
22.42	.883
41.70	1.641
75.00	2.950
0.8mm ²	18GA
3.86	.152
4.01	.158
6.37	.251
6.43	.253
8.50	.335
8.63	.340



NEGATIVE GROUND ONLY

METRIC

WIRE COLOR	CIRCUIT
BLACK	GROUND
WHITE	LOAD
RED	BATTERY



FRONT VIEW OF KNOB

- NOTES:
1. 12 VOLTS D.C. (14.7 VOLTS MAX)
4 AMPS MAX (UNIT NOT LOAD SENSITIVE)
LAMP OR RESISTIVE LOAD NEGATIVE GROUND ONLY
(GROUND WIRE (BLACK) MUST BE GROUNDED)
 2. PROTECTED FOR REVERSE POLARITY (30 V D.C.)
 3. WEATHERPROOF SEALED
 4. ALL STEEL PARTS PLATED

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECK'D	APPR'D	SCALE	DATE DRAWN
									VAK			1:1	10-3-84
				C	ECN 24372	6/11/86	BL	FINISH					DATE BLUEPRINT
				B	ECN 23482	4/8/87	LZ						
				A	23272	10-21-86	AF	TOLERANCES					
					ISSUED	1/31/88	CS	DECIMAL ±	SWITCH, DIMMER, 4 AMP				74600-02
								METRIC ±					

CH-18014-781