

Note: We are enhancing our systems and you may notice duplicate entries/missing/outdated data. During this interim period, please contact our Customer Service at <https://www.ul.com/about/locations>.

Special-purpose Fuses - Component

COMPANY

LITTELFUSE INC

8755 W Higgins Rd, Suite 500
Chicago, IL 60631 United States

E71611

Marking: Company name or tradename "LF" , and model designation.

Note: For additional marking information, refer to the [Guide Information Page](#).

Model(s): 998, ESR3XL-DB, ESR3XL-UB, TLS1-LBE through TLS125-LBE

250, Model(s): AES

Cartridge Fuse, Model(s): JLLS 175 VP

Cartridge fuses, Model(s): KLC-0 through KLC-800, KLPC-200 through KLPC-600, L17T70 through L17T800A, L17T900A through L17T1200A, L25S001 through L25S800, L50S010 through L50S030, L50S035 through L50S800, L70S001 through L70S800, LDC150 through LDC600, LVSP-100-XL, LVSP-10-2, LVSP-10-R, LVSP-15-2, LVSP-15-R, LVSP-20-2, LVSP-20-R, LVSP-30, LVSP-30-2, LVSP-40, LVSP-40-2, LVSP-40-P, LVSP-5-2, LVSP-5-R, LVSP-60, LVSP-60-2, LVSP-80, LVSP-80-2

Cartridge fuses, J case, rated 20, 30, 40, 50, 60A, 58 Vdc, Model(s): 495020, 495025, 495030, 495040, 495050, 495060

Cartridge fuses, low profile J case, rated 20, 30, 40, 50, 60A, 58 Vdc, Model(s): 895020, 895025, 895030, 895040, 895050, 895060

Cartridge fuses, rated 1-100A, 170 Vdc, Model(s): TLS V1 through TLS V100, TLS-1 through TLS-100L, TLS1 through TLS100LB, TLS1 through TLS100LS, TLS1 through TLS100LS-C, TLS-1MB through TLS-100MB

Cartridge fuses, rated 1-125A, 170 Vdc, Model(s): TLS1 through TLS125

Cartridge fuses, rated 1-125A, 170Vdc, Model(s): TLS-1LR through 125LR, TLS-1LSE through TLS125LSE, TLS-1SA through TLS-125SA

Cartridge fuses, rated 1-30A, 600 Vac, Model(s): JLLS 0-30LS, JLLS 0-30V

Cartridge fuses, rated 1-40A, 32 Vdc, Model(s): 257APC

Cartridge fuses, rated 1-600A, 170 Vdc, Model(s): TLN 1-600

Cartridge fuses, rated 20-80A, 32 Vdc, Model(s): 299020, 299025, 299030, 299035, 299040, 299050, 299060, 299070, 299080

Cartridge fuses, rated 20-80A, 58 Vdc, Model(s): 999020, 999025, 999030, 999035, 999040, 999050, 999060, 999070, 999080

Cartridge fuses, rated 2-30A, 32 Vdc / 125 Vac, Model(s): 297, followed by 002 through 030.

Cartridge fuses, rated 3A, 32 Vdc, 32 Vac, Model(s): 257003, 287003

Cartridge fuses, rated 60, 100, 150 and 200A, 32 Vdc, Model(s): 496060, 496100, 496150, 496200

Cartridge fuses, rated 80-200A, 32 Vdc, Model(s): 298, followed by 080 through 200.

Fuses for protection of semi-conductor devices, rated 125 Vac and 125 dc, Model(s): 481, with suffixes 0.18 through 020.

JFHR, Model(s): 0898 Series 0898. Part Number consists of "0", followed by "898", followed by a three-digit number, followed by suffixes

JFHR, Model(s): 0998 Series 0998. Part Number consists of "0", followed by "998", followed by a three-digit number, followed by suffixes

Semi-conductor protection fuses, Model(s): L15S001 through L15S1000, L60S001 through L60S800

Semi-conductor protection fuses rated 125A, 1500Vdc, Model(s): ESR1XL-DB, ESR1XL-UB

Semi-conductor protection fuses rated 450-1400A, 1500Vdc, Model(s): PSX3XL-DB, PSX3XL-DB, PSX3XL-DB-N, PSX3XL-DB-N, PSX3XL-FL, PSX3XL-FL, PSX3XL-FL-N, PSX3XL-FL-N, PSX3XL-UB, PSX3XL-UB, PSX3XL-UB-N, PSX3XL-UB-N

Semi-conductor protection fuses rated 80-630A, 1500Vdc, Model(s): PSX1XL-DB-N, PSX1XL-DB-N, PSX1XL-FL, PSX1XL-FL, PSX1XL-FL-N, PSX1XL-FL-N, PSX1XL-UB, PSX1XL-UB, PSX1XL-UB-N, PSX1XL-UB-N

Semi-conductor protection fuses rated 80-630A, 1500Vdc, Model(s): PSX1XL-DB Cat. No. PSX1XL-FL, PSX1XL-FL-N, PSX1XL-UB, PSX1XL-UB-N, PSX1XL-DB, PSX1XL-DB-N, ESR1XL-UB, ESR1XL-DB.

Semi-conductor protection fuses rated 80-630A, 1500Vdc, Model(s): PSX1XL-DB Cat. No. PSX1XL-FL, PSX1XL-FL-N, PSX1XL-UB, PSX1XL-UB-N, PSX1XL-DB, PSX1XL-DB-N,

Special purpose cartridge fuses rated 35-60A, Model(s): JLLN-L (&), JLLN-LS (&), JLLN-LSE (&), JLLN-V (&)

Special Purpose fuse, rated 100A, 80Vdc, Model(s): CNN100E-U, CNN100E-UD

Special Purpose fuse, rated 150A, 80Vdc, Model(s): CNN150E-U, CNN150E-UD

Special purpose fuse, Rated 30-125A, 70 Vdc and 125A,120Vdc, Model(s): MIDI Series 4998 followed by "M-M6", "M-1M6" or "M-NH".

Special purpose fuse, Rated 60A, 32 Vdc, Model(s): 0899

Special purpose fuses, Model(s): CN-275, CNL-100, CNL-100E, CNL-125, CNL-125E, CNL-130, CNL-130E, CNL-150, CNL-150E, CNL-175, CNL-175E, CNL-200, CNL-200E, CNL-225, CNL-225E, CNL-250, CNL-250E, CNL-275, CNL-275E, CNL-300, CNL-325, CNL-35, CNL-350, CNL-35E, CNL-40, CNL-400, CNL-40E, CNL-50, CNL-500, CNL-50E, CNL-60, CNL-60E, CNL-80, CNL-80E, CNN- 200 E, CNN- 350 E, CNN-10, CNN-100, CNN-100 E, CNN-125, CNN-125 E, CNN-150, CNN-150 E, CNN-175, CNN-175 E, CNN-200, CNN-225, CNN-225-E, CNN-250, CNN-250 E, CNN-275 E, CNN-300, CNN-300 E, CNN-325, CNN-325 E, CNN-35, CNN-35 E, CNN-350, CNN-40, CNN-40 E, CNN-400, CNN-400 E, CNN-50, CNN-50 E, CNN-500, CNN-500 E, CNN-60, CNN-60 E, CNN-600, CNN-700, CNN-700 E, CNN-80, CNN-80 E, CNN-800, CNN-800 E, CNN-90, CNN-90 E

Special Purpose Fuses 30-175A, 32VDC, Model(s): HSB

Special Purpose fuses rated 40-63A, 250/500 Vac, Model(s): 606 with or without one prefix followed by suffix numbers 040. through 063. with or without additional suffix letters and/or numbers, may be followed by P may be followed by TH or THL

Special Purpose fuses rated 40-63A, 300/500 Vac and 500Vdc, Model(s): 607 with or without one prefix followed by numbers 040 through 063 with or without additional suffix letters and/or numbers, may be followed by P, may be followed by TH or THL, may be followed by 500 or 500L.

Special purpose fuses, rated 10-800A, 48 Vdc, Model(s): 581

Special Purpose Fuses, rated 2, 3, 4, 5, 7.5, 10A, 350 Vac, Model(s): 446002, 446002P, 446003P, 446004, 446004P, 446005, 446005P, 446010, 446010P, 44607.5, 44607.5P, 447002, 447002P, 447003, 447003P, 447004, 447004P, 447005, 447005P, 447010, 447010P, 44707.5, 44707.5P

Special purpose fuses, rated 20-100A, 75 Vdc/1000A, 80Vdc/500A, Model(s): 883F

Special purpose fuses, rated 2-30 A, 58 Vdc, Model(s): 997

Special purpose fuses, rated 3/4A and 5A, 600V AC/DC, Model(s): KLKD.750.HXL, KLKD005.HXL

Special Purpose Fuses, rated 3A, 140 Vac, Model(s): 446003

Special purpose fuses, rated 450-1250A, 700Vac/600Vdc, 1400A, 700Vac/600Vdc, 1500-1800A,650Vac/500Vdc, 2000A, 600Vac/500Vdc, 2250A, 550Vac/450Vdc, Model(s): PSR033DL, PSR033DS, PSR033FL, PSR033FS, PSR033FS H, PSR033UL, PSR033US

Special purpose fuses, rated 450-1250A, 700Vac/600Vdc, 1400A, 700Vac/600Vdc, 1500-1800A,650Vac/500Vdc, 2000A, 600Vac/500Vdc, 2250A, 550Vac/450Vdc, Model(s): PSR033FL H Series PSR033FL, PSR033FL_H, PSR033FS, PSR033FS_H, PSR033DL, PSR033DS, PSR033US, PSR033UL.

Special purpose fuses, rated 50-60A, 480 Vac, Model(s): SLC-BD

Special purpose fuses, rated 60-100A, 75 Vdc, Model(s): 881F+

Special purpose fuses, rated 60-125A, 75 Vdc, Model(s): 880+

Special purpose fuses, rated 60-125A, 75 VDC, Model(s): 881+

Special Purpose Fuses, type MIDI, Model(s): 498, followed by 040 through 100, may be followed by M, MXT or MXT-CN.

Special purpose semi-conductor protection fuses, rated 1000A, 700Vac/400Vdc, Model(s): L070SQ33FL1000

Special purpose semi-conductor protection fuses, rated 1000A, 700Vac/500Vdc, Model(s): L070SQ32FL1000

Special purpose semi-conductor protection fuses, rated 1100A, 700Vac/400Vdc, Model(s): L070SQ33FL1100

Special purpose semi-conductor protection fuses, rated 1100A, 700Vac/500Vdc, Model(s): L070SQ32FL1100

Special purpose semi-conductor protection fuses, rated 1250A, 700Vac/400Vdc, Model(s): L070SQ33FL1250

Special purpose semi-conductor protection fuses, rated 1400A, 700Vac/400Vdc, Model(s): L070SQ33FL1400

Special purpose semi-conductor protection fuses, rated 1500A, 600Vac/400Vdc, Model(s): L060SQ33FL1500

Special purpose semi-conductor protection fuses, rated 1600A, 600Vac/400Vdc, Model(s): L060SQ33FL1600

Special purpose semi-conductor protection fuses, rated 160-450A, 1300Vac/1000Vdc, 500-550A, 1200Vac/900Vdc, 630A, 1100Vac/900Vdc, Model(s): PSR071FL, PSR071FS, PSR071UL

Special purpose semi-conductor protection fuses, rated 160-450A, 1300Vac/1000Vdc, 500-550A, 1200Vac/900Vdc, 630A, 1100Vac/900Vdc, Model(s): PSR071DL Cat. No. PSR071FL, PSR071FS, PSR071DL, PSR071UL

Special purpose semi-conductor protection fuses, rated 1800A, 600Vac/400Vdc, Model(s): L060SQ33FL1800

Special purpose semi-conductor protection fuses, rated 200-800A, 700Vac/600Vdc, Model(s): PSR031DL

Special Purpose Semi-Conductor Protection Fuses, Rated 200-800A, 700Vac/600Vdc, Model(s): PSR031DS, PSR031FL, PSR031FS, PSR031UL, PSR031US

Special purpose semi-conductor protection fuses, rated 2-30A, 58 Vdc, Model(s): 891

Special purpose semi-conductor protection fuses, rated 250-630A, 1300Vac/1000Vdc, 700-800A, 1200Vac, 900-1000A, 900Vac, Model(s): PSR072DL, PSR072FL, PSR072FS, PSR072UL

Special purpose semi-conductor protection fuses, rated 250A, 700Vac/500Vdc, Model(s): L070SQ30FL0250

Special purpose semi-conductor protection fuses, rated 315-700A, 1300Vac/1000Vdc, 800A, 1300Vac, 900-1100A, 1050Vac, 1250-1400A, 1000Vac, Model(s): PSR073DL, PSR073FL, PSR073FS, PSR073UL

Special purpose semi-conductor protection fuses, rated 315A, 700Vac/500Vdc, Model(s): L070SQ30FL0315

Special purpose semi-conductor protection fuses, rated 350A, 700Vac/500Vdc, Model(s): L070SQ30FL0350

Special purpose semi-conductor protection fuses, rated 35-800A, 500Vac/500Vdc, Model(s): L50QS

Special purpose semi-conductor protection fuses, rated 35-800A, 700Vac/700Vdc, Model(s): L70QS

Special purpose semi-conductor protection fuses, rated 35-800A, 750Vdc, Model(s): L75QS

Special purpose semi-conductor protection fuses, rated 400-1100A, 700Vac/600Vdc, 1250-1500A, 500Vac/450Vdc, Model(s): PSR032DL, PSR032FL, PSR032FS, PSR032UL, PSR032US

Special purpose semi-conductor protection fuses, rated 400-1100A, 700Vac/600Vdc, 1250-1500A, 500Vac/450Vdc, Model(s): PSR032DS

Special purpose semi-conductor protection fuses, rated 400A, 700Vac/500Vdc, Model(s): L070SQ30FL0400

Special Purpose Semi-Conductor Protection Fuses, rated 40-550A, 700Vac/600Vdc, 630A, 700Vac/550Vdc, Model(s): PSR030DS, PSR030FL, PSR030FS, PSR030UL, PSR030US

Special Purpose Semi-Conductor Protection Fuses, rated 40-550A, 700Vac/600Vdc, 630A, 700Vac/550Vdc, Model(s): PSR030DL Cat. No. PSR030FL, PSR030FS, PSR030DL, PSR030DS, PSR030US, PSR030UL

Special purpose semi-conductor protection fuses, rated 450A, 600Vdc, Model(s): L125SQ71FL0450

Special purpose semi-conductor protection fuses, rated 450A, 700Vac/500Vdc, Model(s): L070SQ30FL0450

Special purpose semi-conductor protection fuses, rated 500A, 700Vac/500Vdc, Model(s): L070SQ30FL0500

Special Purpose Semi-Conductor Protection Fuses, rated 50-315A, 1300Vac/1000Vdc, 350A, 1200Vac/1000Vdc 400A, 1200Vac/900Vdc, Model(s): PSR070UL

Special Purpose Semi-Conductor Protection Fuses, rated 50-315A, 1300Vac/1000Vdc, 350A, 1200Vac/1000Vdc, 400A, 1200Vac/900Vdc, Model(s): PSR070DL, PSR070FS

Special purpose semi-conductor protection fuses, rated 550A, 700Vac/500Vdc, Model(s): L070SQ30FL0550

Special purpose semi-conductor protection fuses, rated 630A, 700Vac/400Vdc, Model(s): L070SQ33FL0630

Special purpose semi-conductor protection fuses, rated 630A, 700Vac/500Vdc, Model(s): L070SQ32FL0630

Special purpose semi-conductor protection fuses, rated 700A, 700Vac/400Vdc, Model(s): L070SQ33FL0700

Special purpose semi-conductor protection fuses, rated 700A, 700Vac/500Vdc, Model(s): L070SQ32FL0700

Special purpose semi-conductor protection fuses, rated 800A, 700Vac/400Vdc, Model(s): L070SQ33FL0800

Special purpose semi-conductor protection fuses, rated 800A, 700Vac/500Vdc, Model(s): L070SQ32FL0800

Special purpose semi-conductor protection fuses, rated 900A, 600Vac/550Vdc, Model(s): PSR031DS

Special Purpose Semi-Conductor Protection Fuses, Rated 900A, 600Vac/550Vdc, Model(s): PSR031DL, PSR031FL, PSR031FS, PSR031UL, PSR031US

Special purpose semi-conductor protection fuses, rated 900A, 700Vac/400Vdc, Model(s): L070SQ33FL0900

Special purpose semi-conductor protection fuses, rated 900A, 700Vac/500Vdc, Model(s): L070SQ32FL0900

Special Purpose Semi-Conductor Protection Fuses, rated rated 50-315A, 1300Vac/1000Vdc, 350A, 1200Vac/1000Vdc, 400A, 1200Vac/900Vdc, Model(s): PSR070FL

(&) - Followed by 35 through 60.

(*) - with or without one prefix followed by numbers 040 through 063 with or without additional suffix letters and/or numbers, may be followed by P, may be followed by TH or THL, may be followed by 500 or 500L.

+ - With or without one prefix and with or without additional suffixes

Last Updated on 2024-01-30

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL Solutions' Follow - Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL Solutions' Follow - Up Service. Always look for the Mark on the product.

UL Solutions permits the reproduction of the material contained in Product iQ subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from Product iQ with permission from UL Solutions" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "©2024 UL LLC."