



REVISION		
REV	DATE	DESCRIPTION
A	8/22/22	525592GCP - RELEASE MRY

12.95 ^{+0.13}/_{-0.00}
 [0.510 ^{+0.005}/_{-0.000}]

NOTE:
 1. MEASUREMENT TAKEN AT END OF TERMINALS

LEAD-FREE SOLDERING PROFILE
 PRE-HEAT: ABOVE 130°C FOR 75 SECONDS MAX
 REFLOW: 278°C FOR 8 SECONDS MAX
 TIME: 250 SECONDS MAX
 MAX TEMP: 280°C

<S>	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE
●	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
⊠	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.

A

MATL SPEC		FINISH	
DRW JMoler	DATE 8/15/2022	SCALE NTS	FINISH GOOD WT GRAMS/PIECE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994

3RD ANGLE PROJECTION	
----------------------	--

TITLE	JLLN-LS 35-60A OUTLINE
-------	------------------------

Littelfuse CHICAGO, ILLINOIS 60631	REVISION A	DRWG NO. OL-JLLN060-LS	SHEET 1 OF 1
--	----------------------	----------------------------------	--------------