

Diodes & Resistors

Specialty Products



ATO® Diodes

Specifications

Operating Temperature:	-40°C to +125°C
Power Rating:	35 A*
Terminals Material:	Brass Tin Plated
Terminals Retention:	Thermoplastic (UL 94V0 Rated)
Housing Material:	Thermoplastic (UL 94V0 Rated)

Additional Information



Resources



Samples



MINI® Diodes

Specifications

Operating Temperature:	-40°C to +125°C
Power Rating:	35 A*
Terminals Material:	Brass Tin Plated
Terminals Retention:	Thermoplastic (UL 94V0 Rated)
Housing Material:	Thermoplastic (UL 94V0 Rated)

Additional Information



Resources



Samples


Ordering Information

Part Number	Current Rating (A)	Type	Housing Material Color	Peak Inverse Voltage (Volts)	Package Size
02400103Z	1	ATO	Black	400	1500
02400113P	1	MINI	Black	400	2000
02400115P	1	MINI	Green	1000	2000
02400119P	1	MINI	Black	400	2000
02400103LXN	1	ATO	Black	400	50
02400104LXN	1	MINI	Black	400	50
02400113XP	1	MINI	Black	400	1

*1 A Diode in ATO® size housing. The cathode connector is rotated 90°

Diodes & Resistors

Specialty Products



MINI® Resistors

Specifications

Operating Temperature:	-40°C to +125°C
Power Rating:	up to 1/2 W
Terminals Material:	C.R.S. (Ni/Zn Plated)
Terminals Retention:	25 N
Housing Material:	Thermoplastic

Additional Information



Resources



Samples

Ordering Information

Part Number	Type	Housing Material Color	Resistance (ohm)	Wattage (Watt)	Package Size
02400106P	MINI	Grey	620	1/2	2000
02400108P	MINI	Blue	5.1K	1/4	2000
02400112P	MINI	Green	121	1/2	2000
02400118P	MINI	Grey	500	1/2	2000

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <https://www.littelfuse.com/legal/disclaimers/product-disclaimer.aspx>