


0.020" ± 0.002" DIAMETER,
24 AWG, TINNED CCS,
1.0" LONG MINIMUM



RESISTANCE @ +25°C = 10,000 Ω ± 5%
RESISTANCE/TEMPERATURE CURVE = "J"
BETA "β" (0 TO +50°C) = 3,892°K NOMINAL
TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
DISSIPATION CONSTANT = 2 mW/°C NOMINAL (STILL AIR)
THERMAL TIME CONSTANT = 5 SECONDS NOMINAL (STILL AIR)
THERMAL TIME CONSTANT = 0.5 SECONDS NOMINAL (STIRRED LIQUID)
MAXIMUM OPERATING TEMPERATURE = +300°C

---	ISO RELEASE	11/06/03	DD
"A"	LEAD WIRE WAS 0.020" ± 0.001" DIAMETER & 1.125" LONG NOMINAL	11/06/03	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR CORP. 1832 W. COLLINS AVE. ORANGE, CA 92867 714-639-1000 www.ussensor.com
DRAWN BY	T. SOMERVILLE	
DATE	11/26/90	
REV.	"A"	
LAYER	0 OF 1	
		NTC THERMISTOR
		P/N 103JG1J