


## PS Series Standard Precision Interchangeable Thermistors




### Description

Littelfuse precision interchangeable thermistors are low cost, highly accurate, stable devices designed specifically for temperature sensing and control applications. They are particularly suited for uses where their precision interchangeability eliminates the necessity for costly individual circuit calibration.

### Options

- Non-standard resistance values and tolerances
- Special lead materials and lengths
- Special encapsulants or probe housings

### Dimensions




Dimensions shown in inches.

A	B	C
30AWG 0.010"	0.095" Max	1.5" Min

### Features

- High accuracy
- Fast thermal response
- Low cost
- Small size
- Epoxy encapsulated
- High stability
- Long life
- R/T Curve-matched

### Part Numbering System



Note: Not all combinations of Part Number codes are available. Contact Littelfuse for details.

## PS Series Standard Precision Interchangeable Thermistors

### Specifications

Part Number	Resistance Ohms @25°C	Accuracy (±°C) 0-70°C	R-T Curve	Temperature Coefficient (% / °C) @ 25°C	Beta (K) 0-50°C	Dissipation Constant, Nominal (mW/°C)	Thermal Time Constant, Max. - Still Air (seconds)	Thermal Time Constant, Max. - Well Stirred Oil (seconds)	Temperature Rating (°C)	Storage & Operation Temp for Best L/T Stability (°C)
PS102J2	1000	± 0.1°C	J	-4.4	3892	1	10	1	-80 to +150	-80 to +75
PS222J2	2252	± 0.1°C	J	-4.4	3892	1	10	1	-80 to +150	-80 to +75
PS302J2	3000	± 0.1°C	J	-4.4	3892	1	10	1	-80 to +150	-80 to +75
PS502J2	5000	± 0.1°C	J	-4.4	3892	1	10	1	-80 to +150	-80 to +75
PS602J2	6000	± 0.1°C	J	-4.4	3892	1	10	1	-80 to +150	-80 to +75
PS103G2	10000	± 0.1°C	G	-4.04	3575	1	10	1	-80 to +150	-80 to +75
PS103J2	10000	± 0.1°C	J	-4.4	3892	1	10	1	-80 to +150	-80 to +75
PS203J2	20000	± 0.1°C	J	-4.4	3892	1	10	1	-80 to +150	-80 to +75
PS303J2	30000	± 0.1°C	J	-4.4	3892	1	10	1	-80 to +150	-80 to +75
PS503J2	50000	± 0.1°C	J	-4.4	3892	1	10	1	-80 to +150	-80 to +75
PS503R2	50000	± 0.1°C	R	-4.68	4140	1	10	1	-80 to +150	-80 to +75
PS104J2	100000	± 0.1°C	J	-4.4	3892	1	10	1	-80 to +150	-80 to +75
PS104R2	100000	± 0.1°C	R	-4.68	4140	1	10	1	-80 to +150	-80 to +75

**Disclaimer Notice** - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics)