


MM IN
 0.25 010
 6.35 250
 25.4 990
 28.95 1140
 31.75 1250
 35.81 1410

M524



NOTES :

- 1. ALL METAL PARTS TO BE BRASS UNLESS OTHERWISE NOTED.
- ② 2. CAP AND HARDWARE SHIPPED LOOSE

METRIC

DO NOT SCALE

| LET | WAS | DATE | BY | LET | WAS | DATE | BY | MATERIAL | DRAWN | CHECKED | APPRV D | SCALE | DATE DRAWN |
|-----|-----|------|----|-----|---------------------------|----------|-----|---------------------------|--|---------|---------|-------|----------------|
| | | | | | | | | — | EA | RJA | | 1:1 | 2-6-64 |
| | | | | | | | | FINISH | 20 OLD COLON ENNE SOU BOS OR US 02 2 | | | | DATE BLUEPRINT |
| | | | | G | ECN #19173 | 5/13/61 | JRF | — | | | | | |
| | | | | F | ECN 27164 ADDED CUTOUT | 12-31-62 | Jap | TOLERANCES | MOM. SWITCH NO | | | | M524 |
| | | | | E | REDRAWN | 3-24-67 | ZU | DECIMAL ± METRIC ±0.25 | | | | | |

CH 188(4 78)