



- NOTES:
- MATERIALS:
 COVER: CRYSTAL-CLAEAR POLYCARBONATE
 BODY: BLACK POLYAMIDE, GLASS FIBER REINFORCED
 CONTACT SECURING: WHITE POLYAMIDE, GLASS FIBER REINFORCED
 CONTACTS: TIN PLATED BRASS, PLATING THICKNESS 8-10µ
 - INSERTION FORCE: 20-50N
 - EXTRACTION FORCE: 12-50N

METRIC
ASSEMBLY

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
		UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES		
		UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.		
⊙		DENOTES CRITICAL CHARACTERISTICS.		
CPK		DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE		
ST		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS		
CP		DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE		

COPIES TO		MATERIAL SPEC		REFER TO NOTES	
1	9	18			
2	10	19			
3	12	20			
4	13	21	DATE	11/18/13	SCALE
5	14	23	FYUE		1:1
6	15	33	CHK		SUPER DR
7	16	43	APPD		FINISH GOOD WT
8	17	53			GRAMS/PIECE
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)		DIMENSION		UP TO 0.5	UP TO 3
				OVER 3 - 6	OVER 6 - 30
				UP TO 120	UP TO 400
				±0.1	±0.2
				±0.1	±0.3
				±0.1	±0.5
3RD ANGLE PROJECTION		TITLE		A TO BLOCK 5 POSITIONS, VERTICAL CONTACTS	
LITTELFUSE		REVISION		NO.	
LIPA CITY, BATANGAS, PHILIPPINES		A		03500418Z	
		OUTLINE			