



- NOTES:
 1. HOLDER MATERIAL : PVC NATURAL COLOR.
 2. WIRE : 1015 12AWG RED.
 3. RATING : MAX. 30A, 32VDC.
 4. FUSEHOLDERS SHOULD NOT BE PLACED UNDER TENSION IN FINAL APPLICATION

METRIC
ASSEMBLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES
 UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
 © DENOTES CRITICAL CHARACTERISTICS.
 CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
 ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
 CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
-	-	-	-	-
-	-	-	-	-
-	-	-	-	-

COPIES TO		MATL SPEC		REVISION		CHK		APD		
1	9	18	SEE NOTES	A	05/10/12	504880ERA-RELEASED FYUE				
2	10	19	FINISH N/A							
3	12	20								
4	13	21		DRW	DATE	05/02/12	SCALE	1:1		
5	14	23		CHK	DATE		SUPER DR			
6	15	33		DATE		FINISH GOOD WT				
7	16	43		APPD						
8	17	53								
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-fH)										
DIMENSION	0.5 - 3	3 - 6	6 - 30	30 - 120	120 - 400	GRAMS/PIECE				
TOLERANCE	±0.05	±0.05	±0.1	±0.15	±0.2					
3RD ANGLE PROJECTION										
TITLE ATO FUSE HOLDER (SMART GLOW)										
REVISION DRWG. NO. A OL-0FHA0001HXGLO										
LITTELFUSE DES PLAINES, ILLINOIS 60016										