

THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	GCF #521133 NEW RELEASED C.MILLER	07/22/19	E.FERNANDEZ

1"-11 1/2 NPSM CONDUIT  
LOCKNUT(SEE NOTE 5)  
(POINTS TOWARD FLANGE)

WASHER

INSULATOR, BLACK

LOCKWASHER, 2 PL, NOTE 5

STUD 3/8-16  
BOTH ENDS

HEX NUT, 2 PL, NOTE 5

Ø 22.22 [0.875]

Ø 39.69 [1.562]

28.57 [1.125]

14.47 [0.570] TYP

15.87 [0.625]

31.45 [1.238]

30.98 [1.220]

52.32 [2.060]

53.09 [2.090]

Ø 33.32 [1.312]


28.70 [1.130]

28.57 [1.125]

TYPICAL PANEL CUTOUT

NOTES:

1. ALL STEEL PARTS PLATED
2. ALL DIMENSIONS ARE REFERENCE ONLY
3. MOUNTING THREADS 1"-11 1/2 NPSM-  
MOUNTING TORQUE 10.8-13.5 Nm  
(8-10 FT LBS) NOT TO EXCEED  
13.5 Nm (10 FT LBS)
4. STUD 3/8"-16 TIGHTENING TORQUE  
8.1-10.8 Nm (6-8 FT LBS)
5. ALL HARDWARE SUPPLIED IN BAG

INTERPRET DRAWING TO ANSI/ASME Y14.5-1994.	
●	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE
DIMENSION: MM TOLERANCES UNLESS OTHERWISE SPECIFIED ONE PLACE DECIMAL ± 0.5      THREE PLACES DECIMAL ± 0.100 TWO PLACES DECIMAL ± 0.20      ANGULAR ± 2°	
NAME	DATE
DRAWN C.MILLER	07/24/19
CHECKED A.HOANG	7/25/19
-	-
-	-
FORM NO: CVP-PE40-0004 REV A	
THIRD ANGLE PROJECTION	
SIZE B	DWG. NO. OL-46211-01
DO NOT SCALE DRAWING	SCALE 1:1
 <b>Expertise Applied   Answers Delivered</b> <b>TITLE</b> <b>FEED THRU STUD</b>	
OUTLINE REV. A	SHEET 1 OF 1