



NOTES:

- 1. MATERIAL: UL94V-0 GLASS FILLED NYLON
- 2. TEMPERATURE RATING: -40°C TO 125°C

PACKAGING NOTES:

- 1. PARTS ARE PACKED 50 PC PER BAG, 10 BAG PER BOX.

METRIC  
ASSEMBLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.  
DIMENSIONS IN BRACKETS [ ] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

◎	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

LTR		DATE	REVISION		CHK	APD
A		05/16/11	502090	ERA-RELEASE	OPL	

  

COPIES TO	MATERIAL SPEC					
1	9	18	FINISH			
2	10	19				
3	12	20				
4	13	21	DRW	OPL	DATE	05/16/11
5	14	23	CHK		DATE	SUPER DR
6	15	33	APPD		DATE	FINISH GOOD WT
7	16	43	GRAMS/PIECE			
8	17	53	TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)			
DIMENSION		0.5 - 3	UP TO	3 - 6	UP TO	30 - 120
TOLERANCE		+0.1	UP TO	+0.1	UP TO	+0.3
3RD ANGLE PROJECTION		TITLE				
COVER FOR MIDI INLINE HOLDER		REVISION				
A		DRAWG. NO.				
OL-498921-1		OUTLINE				

