

## SE-330HV NEUTRAL-GROUNDING-RESISTOR MONITOR SETTINGS

SE-330HV Model Number: SE-330HV - \_\_\_\_ - \_\_\_\_

SE-330HV Serial Number: \_\_\_\_\_ Revision: \_\_\_\_\_

Substation Identification: \_\_\_\_\_

Transformer Specifications: \_\_\_\_\_

### SE-330 Communications

CHECK ONE	
<input type="checkbox"/>	Local RS-232
<input type="checkbox"/>	Other

### Current Transformer

CHECK ONE	
<input type="checkbox"/>	EFCT (5-A primary rating when connected to sensitive input)
<input type="checkbox"/>	SE-CS30 (30-A primary rating when connected to sensitive input)
<input type="checkbox"/>	Other:

### Current Transformer Connection

CHECK ONE	
<input type="checkbox"/>	Sensitive Input (Terminals 8, 11)
<input type="checkbox"/>	1-A Input (Terminals 9, 11)
<input type="checkbox"/>	5-A Input (Terminals 10, 11)

### Sensing Resistor

CHECK ONE	
<input type="checkbox"/>	ER-15KV
<input type="checkbox"/>	ER-25KV
<input type="checkbox"/>	ER-35KV
<input type="checkbox"/>	ER-72 KV

### Remote Indication

CHECK ONE	
<input type="checkbox"/>	None
<input type="checkbox"/>	RK-232
<input type="checkbox"/>	Other:

### NGR Ratings

Current: \_\_\_\_\_ A

Voltage: \_\_\_\_\_

Time: \_\_\_\_\_

Resistance: \_\_\_\_\_  $\Omega$

Serial No.: \_\_\_\_\_

Mfg.: \_\_\_\_\_

### GF Trip Level

Setting: \_\_\_\_\_ % \_\_\_\_\_ A

### GF Trip Time

Setting: \_\_\_\_\_ s


### VN Trip Level

Setting: \_\_\_\_\_ V

X 1 for 100 k $\Omega$  Sensing Resistor: \_\_\_\_\_

X 5 for 200 k $\Omega$  Sensing Resistor: \_\_\_\_\_

## SE-330HV NEUTRAL-GROUNDING-RESISTOR SETTINGS



### CONFIGURATION SWITCH SETTINGS

		CHECK ONE		CHECK ONE
S1:	Spare			
S2:	Fail-Safe		Non-Fail-Safe	
S3:	Latching GF Trip		Non-Latching GF Trip	
S4:	Latching RF Trip		Non-Latching RF Trip	
S5:	200 k Ω		100 k Ω	
S6:	50 Hz		60 Hz	
S7:	Spare			
S8:	Run		Upgrade	

### System Calibration

Calibration Successful: \_\_\_\_\_

Date (YYYY-MM-DD): \_\_\_\_\_

Calibration Number (if available): \_\_\_\_\_