



XCFR2.E309688
Terminal Blocks - Component

[Page Bottom](#)

Terminal Blocks - Component

[See General Information for Terminal Blocks - Component](#)

LITTELFUSE INC
SUITE 500
8755 W HIGGINS RD
CHICAGO, IL 60631 USA

E309688

Cat. No.	Wire Range	Wire Type	FW	TQ Lb In.	V	A	UG	CA
LD2570-3, LFD25703	2/0-14, Line (4) 4-14, Load	Cu/Al	2	Line 2/0-6: 120 Line 8-14: 40 Load 4-14: 35	600	175(CU), 135(AL)	B,C	2(150), 6 (10 x 8.25 x 4 in.), #
LD0401-3, LFD04013	2/0-14, Line (6) 4-14, Load	Cu/Al	2	Line 2/0-6: 120 Line 8-14: 40 Load 4-14: 35	600	175(CU), 135(AL)	B,C	2(150), 6 (10 x 8.25 x 4 in.), #
LFD55523	500-4 Line 2-6 Load 8-14 Load	Cu/Al	2	Line: 375 Load: 2-6: 50 Load: 8-14: 40	600	380 (Cu)	B,C	2(150), 6 (16 x 12 x 6 in)
LFD55793	500-4 Line 2/0-6 Load 8-14 Load	Cu/Al	2	Line: 375 Load: 2/0-6: 120 Load: 8-14: 40	600	380 (Cu)	B,C	2(150), 6 (16 x 12 x 6 in)
LFD35553	2/0-6 Line 8-14 Line 4-14 Load	Cu/Al	2	Line:2/0-6: 120 Line: 8-14: 40 Load: 4-14: 35	600	350 (Cu)	B,C	2(150), 6 (16 x 12 x 6 in)
LFD35533	500-6 Line 2-6 Load 8-14 Load	Cu/Al	2	Line: 375 Load: 2-6: 50 Load: 8-14: 40	600	380 (Cu)	B,C	2(150), 6 (16 x 12 x 6 in)
LFD35523	500-6 Line 2-6 Load 8-14 Load	Cu/Al	2	Line: 375 Load: 2-6: 50 Load: 8-14: 40	600	380 (Cu)	B,C	2(150), 6 (16 x 12 x 6 in)
LFS25723	2/0-14	Cu/Al	2	2/0-6: 120 8-14: 40	600	175 (Cu)	B,C	2(150), 6 (10 x 8.25 x 4 in)
LFD25702	2/0-14 Line 4-14 Load	Cu/Al	2	Line: 2/0-6: 120 Line: 8-14: 40 Load: 4-14: 35	600	175 (Cu)	B,C	2(150), 6 (10 x 8.25 x 4 in)
LFD55923	500-4 Line 4-14 Load	Cu/Al	2	Line: 375 Load: 35	600	760 (Cu)	B,C	2(150), 6 (16 x 12 x 6 in)
LFD55863	500-4 Line 2/0-6 Load 8-14 Load	Cu/Al	2	Line: 375 Load: 2/0-6: 120 Load: 8-14: 40	600	760 (Cu)	B,C	2(150) 6 (16 x 12 x 6 in)

LFS13003	2-14	Cu/Al	2	2-6: 50 8-14: 40	600	115 (Cu)	B,C	2(125), 6 (10 x 8.25 x 4)
LFD14003	2-14 Line 10-18 Load	Cu/Al	2	Line 2-6: 50 Line: 8-14: 40 Load: 10-16: 7 Load: 18: 5	600	115 (Cu)	B,C	2(125), 6 (10 x 8.25 x 4)
GDB60801Z	8-4/(2)/	Cu	2	13.5/	600	80	B,C	2(105),4
GDB61151Z	Input - No. 8-2; Output - 6 No. 14-4	Cu	2	Input - 31.0; Output - 17.5	600	115	B,C	2(105),4
GDB61153Z	Input - No. 8-2; Output - 6 No. 4-14	Cu	2	Input - 31.0; Output - 17.5	600	115	B,C	2(105),4
GDB63101Z	3/0-350	Cu	2	230	600	310	B,C	2(140),4

Unique Conditions of Acceptability - i.e., This terminal block is intended for use with miscellaneous fuses. These fuses are not intended for branch-circuit overcurrent protection. Markings concerning fuse replacement and location should be considered.

Cat. No.	Suitable Conductors kcmil/AWG		Overcurrent Protection Fuse Required Class/Max Amp Rating						SCCR, RMS Sym, kA	Volts Max
	Line	Load	J	T	RK1	RK5	G	CC		
LD2570-3, LFD25703	2/0-10	4-10	200	200	200	100	—	30	200	600
	2/0-14	4-14	30	30	30	30	—	30	200	600
	2/0-14	4-14	—	—	—	—	60	—	100	600
	2/0-10 str	4-10 str	200	200	200	100	—	30	200	600
LD0401-3, LFD04013	2/0-14 str	4-14 str	30	30	30	30	—	30	200	600
	2/0-14 str	4-14 str	—	—	—	—	60	—	100	600
	10-14 sol	10-14 sol	30	30	30	30	—	30	200	600
	10-14 sol	10-14 sol	—	—	—	—	60	—	100	600
LFD55523	500-4	2-4	600	600	400	200	60	30	100	600
	500-4	2-14	30	30	30	30	60	30	200	600
LFD55793	500-4	2/0-4	400	400	400	200	60	30	200	600
	500-4	2/0-4	30	30	30	30	60	30	200	600
LFD35553	2/0-4	4	400	400	400	200	60	30	200	600
	2/0-14	4-14	30	30	30	30	60	30	200	600
LFD35533	500-4	2	400	400	400	200	60	30	200	600
	500-6	2-14	30	30	30	30	60	30	200	600
LFD35523	500-4	2	400	400	400	200	60	30	200	600
	500-6	2-14	30	30	30	30	60	30	200	600
LFS25723	2/0-6	2/0-6	200	200	200	100	60	30	200	600

LD25702	2/0-10	4-10	200	200	200	100	—	30	200	600
	2/0-14	4-14	30	30	30	30	—	30	200	600
	2/0-14	4-14	—	—	—	—	60	—	100	600
LFD55923	500-4	4	600	600	400	200	60	30	100	600
	2-4	4-14	30	30	30	30	60	30	200	600
LFD55863	500-4	2/0-4	600	600	400	200	60	30	100	600
	2-4	2-14	30	30	30	30	60	30	200	600
LFS13003	2-10	2-10	200	200	200	100	60	30	200	600
LFD14003	2-10	10	200	200	200	60	60	30	200	600
	2-14	10-14	30	30	30	30	60	30	200	600
GDB60801Z	8 - 4	14-10 sol/str	80	—	—	—	—	—	100000	600
GDB61151Z	8 - 2	14-4 sol/str	125	—	—	—	—	—	100000	600
GDB61153Z	8 - 2	14-4 sol/str	125	—	—	—	—	—	100000	600
GDB63101Z	3/0 - 350	14-6 AWG (Top), 14-8 AWG (Mid), 14-2 AWG (Bottom)	350	—	—	—	—	—	100000	600

Marking: Company name and catalog designation (catalog designation may appear on shipping carton).

Last Updated on 2013-07-01

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2014 UL LLC

When the UL Leaf Mark is on the product, or when the word "Environment" is included in the UL Mark, please search the [UL Environment database](#) for additional information regarding this product's certification.

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2014 UL LLC".