

2506-L	10.000 [254.00]	10.000 [254.00]	0.375 [9.52]	0.375 [9.52]	NONE	NONE	16 GA GPT [1.0 mm sq]	BLACK	0.035 [0.89]
2506-K	18.000 [457.20]	18.000 [457.20]	0.375 [9.52]	0.375 [9.52]	NONE	NONE	16 GA GPT [1.0 mm sq]	BLACK	0.035 [0.89]
2506-J	36.000 [914.40]	36.000 [914.40]	0.375 [9.52]	0.375 [9.52]	NONE	NONE	16 GA GPT [1.0 mm sq]	BLACK	0.035 [0.89]
2506-H	SEE	NOTE	2						0.035 [0.89]
2506-G	10.000 [254.00]	10.000 [254.00]	0.250 [6.35]	0.250 [6.35]	31104	31104	18 GA GPT [0.8 mm sq]	BLACK	0.035 [0.89]
2506-F	10.000 [254.00]	24.000 [609.60]	0.250 [6.35]	0.250 [6.35]	3116	3116	16 GA GPT [1.0 mm sq]	BLACK	0.035 [0.89]
2506-E	6.000 [152.40]	10.000 [254.00]	0.250 [6.35]	0.250 [6.35]	2506-10	2506-10	16 GA GPT [1.0 mm sq]	BLACK	0.035 [0.89]
2506-D	12.000 [304.80]	12.000 [304.80]	0.375 [9.52]	0.375 [9.52]	NONE	NONE	16 GA GPT [1.0 mm sq]	BLACK	0.025-0.032 [0.63-0.81]
2506-C	12.000 [304.80]	12.000 [304.80]	0.375 [9.52]	0.375 [9.52]	NONE	NONE	16 GA GPT [1.0 mm sq]	BLACK	0.047 [1.19]
2506-B	12.000 [304.80]	12.000 [304.80]	0.375 [9.52]	0.375 [9.52]	NONE	NONE	16 GA GPT [1.0 mm sq]	BLACK	0.021 [0.53]
2506-A	12.000 [304.80]	12.000 [304.80]	0.375 [9.52]	0.375 [9.52]	NONE	NONE	16 GA GPT [1.0 mm sq]	BLACK	0.090-0.100 [2.28-2.54]
2506	8.000 [203.20]	8.000 [203.20]	0.375 [9.52]	0.375 [9.52]	NONE	NONE	16 GA GPT [1.0 mm sq]	BLACK	0.035 [0.89]
PT NO	A	B	C	D	TERM A	TERM B	TYPE	COLOR	PANEL
							BOTH WIRES		THK

PROPRIETARY INFORMATION. This Engineering Drawing, and the information contained herein, is proprietary to Cole Hersee Company and may not be disclosed, re-produced, or in any other way transferred or communicated to any other party without the express written consent of an authorized representative of Cole Hersee Company.

Special Characteristics:

(KC) Control Dimension relating to Form - Fit - Function as defined by Cole Hersee Company and/or the Customer

Responsible **NA** Pg. 2 of 2

Description: SOCKET ASSEMBLY