



NO		COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL					
			MATL SPEC	FINISH	
COPIES TO			DATE	SCALE	
1 9 18			1/21/98	1=1	
2 10 19					
3 12 20			DATE	SUPER DRW	
4 13 21					
5 14 23			DATE	RAW STK WT	LBS/M
6 15 33			TOLERANCE UNLESS OTHERWISE SPECIFIED		
7 16 43			TWO PLACE DEC ±.01 FRACTION ±		
8 17 53			THREE PLACE DEC ±.005 ANGULAR ±1°		
TITLE			AUTOFUSE IN-LINE FUSEHOLDER (WITH & W/O 257 SERIES AUTOFUSE)		
LTR		REVISION			
C		38991C-REVISED & REDRAWN ON NEW FORMAT 2/23/98 JMB			
D		38865B-CHG 14 TO 10, BLACK TO ORANGE 5/7/99 PJM			
CP DIMENSIONS - MINIMUM CP VALUE BE WITHIN THE DIMENSIONAL LIMITATIONS ON DRAWING AND INITIALLY LOCATED TO FOR MAXIMUM TOOL LIFE. CP DIMENSIONS - MINIMUM CP VALUE BE WITHIN THE DIMENSIONAL LIMITATIONS ON DRAWING AND INITIALLY LOCATED TO FOR MAXIMUM TOOL LIFE.					
		CHK			APD
			 DES PLAINES, ILLINOIS 60016 D ENGINE NO. OAFH000 SERIES		