




M8 X 1.25	354539		108 LB.-IN (12.0 N.m)
"A" TAP	LITTELFUSE N ^o		RECOMENDED TORQUE



"A" TAP THRU
(SEE CHART)

NOTE:

ALL DIMENSIONS ARE IN MILLIMETERS.
ENGLISH DIMENSIONS IN [].

CERTIFICATION OF
COUNTRY OF ORIGIN
REQUIRED

COPIES TO		MAT'L. SPEC.		FINISH		SCALE		SUPER. DR.		RAW STK. WT.		LBS./M	
1	2	3	4	5	6	7	8	9	10	11	12	13	14
18	19	20	21	22	23	24	25	26	27	28	29	30	31
32	33	34	35	36	37	38	39	40	41	42	43	44	45
TOLERANCE UNLESS OTHERWISE SPECIFIED													
TWO PLACE DEC. ± .50mm [.020] FRACTION ±													
THREE PLACE DEC. ± .25mm [.010] ANGULAR ±													
TITLE													
Power Tap Module													
Litelfuse [®]													
800 E. NORTHWEST HIGHWAY DES PLAINES, ILLINOIS 60016													
DRWG. NO. D- 03540539Z													

LTR	REVISION	CHK.	APD.
A	06559 - RELEASED OCTOBER 25, 94 G.S.	Geo	AA
B	36988C - ADD METRIC DIM. 7-19-95 RFR	Co	Co
C	37055D - CHANGE TITLE 8-19-95 JCU	TRR	Co
D	000807ER - RE-INSTATE 10/09/09 J.U.		

DRAWING NO.