


90047
90048



FRONT VIEW OF 90047 LESS
FACE NUT

90048 SAME
AS 90047 EXCEPT
ENGINE IMPRINTING AS SHOWN
ON RED PLUNGER

ENGINE
STOP

20 AMPS	24 VDC
35 AMPS	12 VDC
CURRENT RATING	

NOTES.

1. ALL STEEL PARTS EITHER ZINC PLT. WITH DICH. DIP. OR CAD. PLT.
2. ALL CONTACT SURFACES SILVER
3. SWITCH TO FIT PANELS .04 TO .10 THK.

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPROV'D	SCALE	DATE DRAWN
				D	ADD 500 510	21330	3-10-81	NOTED	RW	RE		1"=1"	6-26-72
				C	REV. 19288	1-20-76	KG	FINISH	COLE-HERSEE COMPANY BOSTON, MASS 02127, U.S.A.				DATE BLUEPRINT
				B	ADD RATING	8-21-75	RF	NOTED					
				A	66 REF. 117846	8-23-72	CT	TOLERANCES FRACTIONAL ± DECIMAL ±.01	MOMENTARY SWITCH				90047
					ISSUED	6-29-72	B						