PART NUMBER
GDBAD211Z







REVISION		
REV	DATE	DESCRIPTION
A	4/22/16	515747GCP - RELEASE PER EM2806 MRY
B	1/30/17	516960ECP/D - UPDATE SIDE PRINTING MRY

NOTES:

1. AGENCY INFORMATION:
   UL FILE NO. E482231
   CSA FILE NO. 700111

2. MATERIALS:
   INSULATOR-HIGH IMPACT THERMOPLASTIC,
   TEMP RATING 125°C (257°F)
   CONNECTOR-ALUMINUM

3. TERMINATION:
   LINE: 2-14 AWG
   LOAD: 2-14 AWG
   WIRE COMBINATIONS PER UL FILE

4. RATINGS:
   600V
   MAXIMUM AMP PER POLE-115A
   BASED ON NEC WIRE RATING CODE, 75°C WIRE

   PROVIDES SPACINGS FOR USE IN FEEDER CIRCUITS
   AT 251-600V PER UL508A

5. FOR DIMENSIONS OF MULTILINE STACK-UPS, ADD 19.05 [0.75] TO OVERALL WIDTH, CENTERLINE SPACING OF 19.05 [0.75] POLE TO POLE.

6. TORQUE:
   LINE/LOAD: 2-3 AWG 50 IN-LB
   4-6 AWG 45 IN-LB
   8 AWG 40 IN-LB
   10-14 AWG 35 IN-LB

TOLERANCE (UNLESS OTHERWISE SPECIFIED):
1 PLACE ± 2.5mm [0.1]
2 PLACE ± 0.76mm [0.03]
3 PLACE ± 0.381mm [0.015]

●	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
⟨ST⟩	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.

B

MATL SPEC		FINISH	
DRW myork	DATE 1/21/2016	SCALE NTS	FINISH GOOD WT GRAMS/PIECE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [ ] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994

3RD ANGLE PROJECTION

TITLE
600V DISTRIBUTION BLOCK 115A OUTLINE

Littelfuse®
CHICAGO, ILLINOIS 60631

REVISION	DRWG NO.	SHEET 1 OF 1
B	OL-GDBAD21	