





PART NO.	MAX. CONTINUOUS OPERATING VOLTAGE (AC)	NOMINAL AC VOLTAGE	ELECTRICAL SYSTEM
SPDN-B120-1P	180	120	SINGLE PHASE
SPDN-B120-2S	180	240/120	SPLIT PHASE
SPDN-B120-3Y	150	208/120	3 PHASE WYE
SPDN-B240-1P	350	240	SINGLE PHASE
SPDN-B240-3D	275	240	3 PHASE DELTA
SPDN-B277-3Y	350	480/277	3 PHASE WYE
SPDN-B480-3D	550	480	3 PHASE DELTA

REVISION		
REV	DATE	DESCRIPTION
A	5/16/23	526444GCP - RELEASE MRY



WIRING CONFIGURATION



- NOTES:
- STANDARD LEAD LENGTH: 18-20"
 - ENCLOSURE RATING: POLYCARBONATE 4X

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
<S>	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE			
●	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.			C
MATL SPEC			FINISH	
DRW myork	DATE 2/28/2023	SCALE NTS	FINISH GOOD WT GRAMS/PIECE	
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994				
3RD ANGLE PROJECTION				
				
TITLE				
SURGE PROTECTION DEVICE, UL TYPE 1 OUTLINE				
 Littelfuse® CHICAGO, ILLINOIS 60631		REVISION A	DRWG NO. OL-SPDN-B	SHEET 1 OF 1