







SECTION B - B



SECTION A - A



METRIC
ASSEMBLY

- NOTES:
1. MATERIALS:
COVER: CRYSTAL-CLAEER POLYCARBONATE
BODY: BLACK POLYAMIDE, GLASS FIBER REINFORCED
CONTACT SECURING: WHITE POLYAMIDE, GLASS FIBER REINFORCED
CONTACTS: TIN PLATED BRASS, PLATING THICKNESS 8-10u

BILL OF MATERIAL			
NO	COMPONENT NO	DESCRIPTION	QTY/M U/M
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES			
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.			
⊙	DENOTES CRITICAL CHARACTERISTICS.		
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE		
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS		
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE		

COPIES TO		MATL SPEC		REFER TO NOTES	
1	9	18	FINISH		REFER TO NOTES
2	10	19	DRW	FYUE	DATE 8/16/13
3	12	20	CHK		DATE SUPER DR
4	13	21	APPD		DATE FINISH GOOD WT
5	14	23	GRAMS/PIECE		
6	15	33	TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-PH)		
7	16	43	DIMENSION	0.5 - 3	UP TO OVER UP TO OVER UP TO OVER
8	17	53	TOLERANCE	+0.1	+0.1 ±0.2 ±0.3 ±0.5
3RD ANGLE PROJECTION		TITLE		ATO BLOCK 5 POSITIONS, HORIZONTAL CONTACTS	
Littelfuse		REVISION		OUTLINE	
LIPA CITY, BATANGAS, PHILIPPINES		A		03500417Z	