



NOTES:

- 1) BASE: UL94V0, GLASS FILLED PA66, BLACK
M5 STUDS: ZINC-PLATED STEEL
COVER: THERMOPLASTIC ELASTOMER, BLACK
HEX NUTS: STEEL
LOCK WASHERS: STEEL
2) MAX FUSE RATING: 200A
3) M5 STUD TORQUE: 3-5.0 Nm MAX
MOUNTING TORQUE: WITH M4 BOLTS AND WASHERS: 5Nm MAX
4) TEMPERATURE RATING: -40°C TO 125°C



METRIC

ASSEMBLY

[illegible]