







LTR	DATE	REVISION	CHK	APD
A	01/22/14	510030ERA-RELEASE FYUE		
B	07/18/14	510793ECA-ADD DIMENSTONS FYUE		



-				
-				
-				
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
				
COPIES TO		MATL SPEC		
		Mapex PA66 A0520FN-03 (30%GF)		
1	9	18	FINISH	
2	10	19	NONE	
3	12	20		
4	13	21	DRW	FYUE
5	14	23	DATE	01/22/14
6	15	33	SCALE	1:1
7	16	43	CHK	DATE
8	17	53	DATE	SUPER DR
			APPD	DATE
			DATE	FINSH GOOD WT
GRAMS/PIECE				
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-MH)				
DIMENSION	0.5 - 3	UP TO 3 OVER 3 - 6	UP TO 6 OVER 6 - 30	UP TO 30 OVER 30 - 120
TOLERANCE	+0.1	+0.1	+0.2	+0.3
UP TO 400 OVER 400				
3RD ANGLE PROJECTION		TITLE		
		BASE		
		REVISION	DRWG. NO.	OUTLINE
CHICAGO, USA 773-628-1000		B	OL-868-163	

METRIC
COMPONENT

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED (rev C)