

(b) the same company as the company that made the first sale of the article; and
 (c) the same person as the person who made the first sale of the article.

4.82 DIA. LOCATING PIN,
STEEL

21.84 R.

HENCOL SEAL-13
SHOWN SHADED

(N)
DATE CODE MARKED -
ON SIDE OF CASE AT
RANDOM

DASH, TAIL, HEAD
& REAR LAMPS

DASH-TAIL & HEAD
LAMPS

DASH & TAIL LAMPS

OFF

1/2 - 20 UNF - 2A THD.
BUSHING

O-RING —
(SEE NOTE 4A)

SHAFT, STEEL

—2.28

MOUNTING STEM DETAIL

LEVER, ZINC-DIE CAST

HEX NUT, ZINC PLT: (SEE NOTE #B).

—INT. TOOTH LOCKWASHER, STEEL

—CASE, STEEL

SCREW, 8-32UNC-2A X 7.92 LG., STEEL (4 REQ'D)

SHAKEPROOF LOCKWASHER, STEEL (4 REQ'D)

- TERMINAL INSULATOR, BAKELITE

-HEN COL SEAL#13

HENCO —
SEAL # 13

NOTES:

1. SILVER LAMINATED SHOULDER RIVETS STATIONARY CONTACTS; SOLID SILVER RIVETS MOVING CONTACT.
2. MELAMINE LINER
3. NUMBER OF POLES 1
NUMBER OF THROWS 3
4. SEALING:
A O-RING AT MTG. STEM & SHAFT
B GASKET SEAL AT TERMINAL INSULATOR
5. ALL STEEL PARTS PLATED
6. RATING:
12 V | 30 AMPS TOTAL
24 V | 18 AMPS TOTAL
7. LIFE @ RATED CURRENT
MAKE & BREAK
12V, & 24V - 100000 CYCLES/MN.
8. INSTALLATION TORQUE 6.75 Nm [5 FT. LBS.]

8: INSTALLATION TORQUE 6.75Nm [5FT.LBS]

DO NOT SCALE

DATE DRAWN
11-4-93

DATE BLUEPRINT

Substrate

72058-02

METRIC

LET.	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPROVED	SCALE	EX 25396-B	DATE DRAWN
									TJH	AP		1:1		11-4-93
					N ECN 02356	7/24/92	JHL	FINISH						DATE BLUEPRINT
					M ECN 02356	1/21/93								
					L ECN 23575	1/21/93								
								TOLERANCES						
								DECIMAL ±						
								METRIC ±						
									TRACTOR COMBINATION					72058-02
									LIGHT SWITCH					