


MM	IN
3.96	.156
4.76	.187
9.52	.375
14.47	.570
17.46	.687
18.25	.718
20.82	.820
21.08	.830
28.97	1.140
31.75	1.250
6.35	.250

M-485



NOTES:

1. ALL METAL PARTS TO BE BRASS 9.
UNLESS OTHERWISE SPECIFIED
2. INSERTION PRESSURE 3 1/2 # TO 5#

METRIC

⑦ 3. ALL HARDWARE SHIPPED LOOSE

10 AMP5 @ 12VDC

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPR'L	SCALE	DATE DRAWN
								NOTED	JE			1:1	3-3-50
								FINISH NOTED	 Cole Hersee Co. 20 DILL C. J. DRURY AVENUE SOUTH BOSTON, MA. U.S.A. 02127				DATE BLUEPRINT
				T	ECN # 99193	5/13/99	JE	TOLERANCES DECIMAL $\pm .015$ METRIC $\pm .010$	SWITCH, MOMENTARY N.O.				M-485
				S	ECN # 27164 ADDED CUTOUT	12-31-97	Jmp						
				R	REDRAWN	8/6/90	BL						

CH-188(4-78)

Confidential Property of Cole Hersee