


USP8798 Thermistor Probe




Description

Littelfuse offers Copper clip-on pipe probe housings suitable for a wide range of temperature sensing applications. If the dimensions on this product won't work for your requirements, please contact us for further assistance.

Features

- Tight Tolerance
- Supplied with a Copper Plated Clip designed to affix to a 0.250" Diameter Pipe
- Moisture Resistant
- 105°C Max Operating Temperature

Dimensions




Dimensions in inches.

A	B	C	D	E	F
0.157" ± 0.060" Strip	0.787" ± 0.045"	0.394" ± 0.040"	0.167" ± 0.015"	50.75" ± 2.0"	0.220" Nom

G	H	I	J	K
0.465" Nom	0.165" Nom	0.244" Nom	0.224" Nom	0.020" Nom

Part Numbering System



Note: Not all combinations of Part Number codes are available. Contact Littelfuse for details.

Specifications

Part Number	Resistance Ohms @25°C	R-T Curve	Temperature Coefficient (% / °C) @ 25°C	Beta (K) 0-50°C	Temperature Rating (°C)
USP8798	10000	J	-4.4	3892	-55 to +105

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: www.littelfuse.com/disclaimer-electronics