

Parameter	Rating	Units
Blocking Voltage	30	V _P
Load Current	1.2	A _{DC}
On-Resistance (max)	0.25	Ω

Features

- 1500V_{rms} Input/Output Isolation
- Small 4-Pin SOP Package
- Low Drive Power Requirements
- High Reliability
- No EMI/RFI Generation
- Tape & Reel Version Available
- Flammability Rating UL 94 V-0

Applications

- Sensor Circuitry
- Instrumentation
- Multiplexers
- Data Acquisition
- Electronic Switching
- I/O Subsystems
- Meters (Watt-Hour, Water, Gas)
- Medical Equipment—Patient/Equipment Isolation
- Industrial Controls

Description

The CPC1020N is a 30V, single-pole, normally-open (1-Form-A) Solid State Relay. The ultra-low on-resistance of this relay, 0.25Ω, enables high-current operation.

IXYS Integrated Circuits' patented OptoMOS architecture makes available the optically coupled technology necessary to activate the output's efficient MOSFET switches while providing 1500V_{rms} input to output isolation. Control of the isolated output is accomplished by means of the highly efficient infrared LED at the input.


Approvals

- UL Recognized Component: File E76270
- CSA Certified Component: Certificate 1172007
- TUV EN 62368-1: Certificate # B 082667 0008


Ordering Information

Part #	Description
CPC1020N	4-Pin SOP (100/tube)
CPC1020NTR	4-Pin SOP (2000/reel)

Pin Configuration



Switching Characteristics of Normally-Open Devices



Absolute Maximum Ratings @ 25°C

Parameter	Ratings	Units
Blocking Voltage	30	V _p
Input Power Dissipation ¹	75	mW
Input Control Current	50	mA
Peak (10ms)	1	A
Reverse Input Voltage	5	V
Total Power Dissipation ²	400	mW
Isolation voltage, Input to Output	1500	V _{rms}
Operational Temperature, Ambient	-40 to +85	°C
Storage Temperature	-40 to +125	°C

¹ Derate linearly 1.33 mW / °C

² Derate output power linearly 3.33 mW / °C

Absolute Maximum Ratings are stress ratings. Stresses in excess of these ratings can cause permanent damage to the device. Functional operation of the device at conditions beyond those indicated in the operational sections of this data sheet is not implied.

Typical values are characteristic of the device at +25°C, and are the result of engineering evaluations. They are provided for information purposes only, and are not part of the manufacturing testing requirements.

Electrical Characteristics @ 25°C

Parameter	Conditions	Symbol	Min	Typ	Max	Units
Output Characteristics						
Blocking Voltage	I _L =1μA	V _{DRM}	30	-	-	V
Load Current						
Continuous ¹	I _F =2mA	I _L	-	-	1.2	A _{DC}
Peak	t ≤ 10ms	I _{LPK}	-	-	3	A
On-Resistance ²	I _L =1A	R _{ON}	-	0.116	0.25	Ω
Off-State Leakage Current	V _L =30V _p	I _{LEAK}	-	-	1	μA
Switching Speeds						
Turn-On	I _F =5mA, V _L =10V	t _{on}	-	0.48	3	ms
Turn-Off		t _{off}	-	0.65	3	
Output Capacitance	I _F =0mA, V _L =25V, f=1MHz	C _{OUT}	-	33	-	pF
Input Characteristics						
Input Control Current to Activate	I _L =1A	I _F	-	0.13	2	mA
Input Control Current to Deactivate	-	I _F	0.1	-	-	mA
Input Voltage Drop	I _F =5mA	V _F	0.9	1.36	1.5	V
Reverse Input Current	V _R =5V	I _R	-	-	10	μA
Input/Output Characteristics						
Capacitance, Input to Output	V _{IO} =0V, f=1MHz	C _{IO}	-	3	-	pF

¹ Load current derates linearly from 1.2A @ 25°C to 0.58A @ 85°C.


² Measurement taken within 1 second of on-time.

ESD Rating


ESD Rating (Human Body Model)
1000 Volts

PERFORMANCE DATA*


Typical LED Forward Voltage Drop
(N=50, $I_F=5\text{mA}$)




Typical I_F for Switch Operation
(N=50, $I_L=100\text{mA}$)




Typical On-Resistance Distribution
(N=50, $I_F=2\text{mA}$, $I_L=1\text{A}$)




Typical Turn-On Time Distribution
(N=50, $I_F=5\text{mA}$, $I_L=5\text{mA}$)




Typical Turn-Off Time Distribution
(N=50, $I_F=5\text{mA}$, $I_L=5\text{mA}$)




Typical Blocking Voltage Distribution
(N=50)




Typical LED Forward Voltage Drop
vs. Temperature




Typical I_F for Switch Operation
vs. Temperature
($I_L=1\text{A}$)




Typical Load Voltage vs. Load Current
($I_F=2\text{mA}$)




Typical Turn-On Time
vs. LED Forward Current
($I_L=100\text{mA}$)



Typical Turn-Off Time
vs. LED Forward Current
($I_L=100\text{mA}$)




Typical On-Resistance vs. Temperature
($I_F=2\text{mA}$, $I_L=0.5\text{A}$)




*Unless otherwise noted, data presented in these graphs is typical of device operation at 25°C.

PERFORMANCE DATA*


Typical Turn-On Time vs. Temperature
($I_L=100\text{mA}$)




Typical Turn-Off Time vs. Temperature
($I_L=100\text{mA}$)




Maximum Load Current vs. Temperature
($I_F=2\text{mA}$)




Typical Blocking Voltage vs. Temperature
($I_L=1\mu\text{A}$)




Typical Leakage Current vs. Temperature
Measured Across Pins 3&4
($I_F=0\text{mA}$, $V_L=30\text{V}$)



Output Capacitance vs. Load Voltage
($I_F=0\text{mA}$, $f=1\text{MHz}$)



Energy Rating Curve



*Unless otherwise noted, data presented in these graphs is typical of device operation at 25°C.

Manufacturing Information

Moisture Sensitivity



All plastic encapsulated semiconductor packages are susceptible to moisture ingress. IXYS Integrated Circuits classifies its plastic encapsulated devices for moisture sensitivity according to the latest version of the joint industry standard, **IPC/JEDEC J-STD-020**, in force at the time of product evaluation. We test all of our products to the maximum conditions set forth in the standard, and guarantee proper operation of our devices when handled according to the limitations and information in that standard as well as to any limitations set forth in the information or standards referenced below.

Failure to adhere to the warnings or limitations as established by the listed specifications could result in reduced product performance, reduction of operable life, and/or reduction of overall reliability.

This product carries a **Moisture Sensitivity Level (MSL)** classification as shown below, and should be handled according to the requirements of the latest version of the joint industry standard **IPC/JEDEC J-STD-033**.

Device	Moisture Sensitivity Level (MSL) Classification
CPC1020N	MSL 3

ESD Sensitivity



This product is ESD Sensitive, and should be handled according to the industry standard **JESD-625**.

Soldering Profile

Provided in the table below is the **IPC/JEDEC J-STD-020** Classification Temperature (T_C) and the maximum dwell time the body temperature of these surface mount devices may be ($T_C - 5$)°C or greater. The Classification Temperature sets the Maximum Body Temperature allowed for these devices during reflow soldering processes.

Device	Classification Temperature (T_C)	Dwell Time (t_p)	Max Reflow Cycles
CPC1020N	260°C	30 seconds	3


Board Wash

IXYS Integrated Circuits recommends the use of no-clean flux formulations. Board washing to reduce or remove flux residue following the solder reflow process is acceptable provided proper precautions are taken to prevent damage to the device. These precautions include but are not limited to: using a low pressure wash and providing a follow up bake cycle sufficient to remove any moisture trapped within the device due to the washing process. Due to the variability of the wash parameters used to clean the board, determination of the bake temperature and duration necessary to remove the moisture trapped within the package is the responsibility of the user (assembler). Cleaning or drying methods that employ ultrasonic energy may damage the device and should not be used. Additionally, the device must not be exposed to halide flux or solvents.




MECHANICAL DIMENSIONS

CPC1020N




Recommended PCB Land Pattern



Note:

1. Lead dimensions do not include plating: 1000 microinches max.
2. Controlling dimension: mm

CPC1020NTR Tape & Reel



NOTE: All dimensional tolerances per Standard EIA-481-2 except as noted

For additional information please visit our website at: <https://www.ixysic.com>