

Protection Relays & Controls

EL3100 SERIES

Ground-Fault Protection – Grounded/Ungrounded AC •
Systems Ground-Fault & Phase-Voltage Indicator

Accessories

A



Remote LEDs

High-intensity 16-mm IP67 LED lamps
available in red and green colors.

Specifications

Input Voltage	Input L: 208/240 Vac Input H: 480/600 Vac
Dimensions	H 87.0 mm (3.43") W 112.5 mm (4.43") D 56.0 mm (2.2")
Approvals	CSA certified, UL Listed (E340889)
Conformally Coated	Standard feature
Warranty	5 years
Mounting	DIN, Surface

Ordering Information

ORDERING NUMBER	MOUNTING	ACCESSORIES	REQUIREMENT
EL3100-00	DIN, Surface	RK-310X-0Y	Optional

Note: X=R for red LED and G for green LED

Y=0 for no label and 1 for a ground-fault label

Disclaimer Notice – Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/product-disclaimer.