

58328 SERIES ROCKER SWITCHES



Specifications Overview

Voltage Rating:	25A @ 12V DC
Circuitry:	Single Pole, Single Throw
Housing:	Black Plastic
Mounting:	Snap-in matte black bezel through 21.1mm x 36.8mm rectangular Panel Hole, 2.4mm to 4.7mm thick
Ingress Protection:	IP66 (Contact Area)
Actuator:	2-Position, matte black plastic actuator
Lens:	Red
Positions:	Off - On (Up-Down)
Termination:	3 Brass Blades

Description

Littelfuse Rocker Switches are designed for universal applications within harsh environments. Their mounting, body, and actuator features are designed for ease-of-use and extended product lifecycle.

The 58328 Series is our most popular line of LED-enabled rocker switches. These products are single-actuator switches that are commonly used for in-cabin controls, but are also IP66 rated against dust and moisture.

Features and Benefits

- Silver contacts for corrosion resistance
- Bright, long-lasting LED illumination

Web Resources

Download 2D print and technical resources at: littelfuse.com/58328

Ordering Information



PART NUMBER	DESCRIPTION
58328-04 *	Single, Dependent Wide Red-Lens Rocker Switch

* Box and Retail Blister Pack Available

Applications

- Construction Equipment
- Agricultural Equipment
- Material Handling Equipment
- Commercial Vehicles

Dimensions



Visit Littelfuse.com for the most up-to-date product information. Littelfuse products are designed for specific applications and should not be used for any purpose (including, without limitation, automotive applications) not expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse product documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse product documentation.