

REV	REVISION RECORD	DATE	APP
"D"	TUBE DIAMETER WAS 0.130" ± 0.005" & TUBE LENGTH WAS 0.235" MAXIMUM	03/08/10	DD
"C"	TUBE DIAMETER WAS 0.130" MAXIMUM	03/04/10	DD
"B"	TUBE LENGTH WAS 0.190" MAXIMUM	01/18/10	DD
"A"	RTD ELEMENT ACCURACY CLASS WAS "A"	01/08/10	DD
NONE	RELEASE TO PRODUCTION	01/08/10	DD

RESISTANCE @ 0°C = 500 Ω ± 0.12%
ACCURACY @ 0°C = ± 0.30°C
DIN 43760 ACCURACY CLASS = "B"
TCR = 3,850ppm/°C
MAXIMUM TEMPERATURE RATING = +150°C

SEE MANUFACTURING SPECIFICATION (LAYER 1)

SCALE NONE

DRAWN BY
DAN DANKERT

DATE 01/08/10

REV. "D"

LAYER 0 OF 2

U.S. SENSOR CORP.
1832 W. COLLINS AVE.
ORANGE, CA. 92867
714-639-1000 www.ussensor.com

RTD PROBE ASSEMBLY

P/N USW2883