
LIQUID LEVEL PROBES & PROBE HOLDERS

LIQUID LEVEL CONTROL ELECTRODES		
Product	**Features**	**Accessory For**
LLP-24 Liquid Level Probe 	Threaded stainless steel probe measuring 24 in. (61 cm) long. Designed for use with PHST-38QTN liquid level control electrodes.	**PHST-38QTN**
PHST-38QTN Probe Holder **P0700-409** Protective Boot  	Designed for use with all conductive liquid level controls. Composed of insulators and metal parts made of number 300 series stainless steel. These internally conductive probe holders are designed for a maximum steam pressure of 240 PSI; 400° F maximum. Maximum voltage from electrode to ground. PHST-38QTN is UL 353 Recognized.	**Series:** **LLC1** **LLC2** **LLC4** **LLC5** **LLC6** **LLC8** **PC-XXX-LLC-CZ** **PC-XXX-LLC-GM** **460-15-100-LLS**

© 2017 Littelfuse Protection Relays & Controls